

修 订	标 记	修 改 描 要	签 名	日 期
REV NO	MARK	REVISION DESCRIPTION	SIGNATURE	DATE
		NEW DWG		2016-03-12

规格说明:Specifications:

电气特性:Electrical:

1. 额定电流: Current Rating
1.5A/contact terminal

2. 额定电压: Voltage Rating
30V DC

3. 接触阻抗:Contact Resistance
30 milliohms MAX

4. 耐电压:Dielectnic Withstanding Voitage:
500 V AC AT Sea Levol

5. 绝缘阻抗:lnsulation Resistance:
1000MEGA ohms MIN

物理性能:Mechanical:

1. 插拔力: Cnector Mate and Unmate Force
Mate force:3.57kgf (MAX)
Unmate force:1.02kgf (MIN)

2. 端子保持力: Terminal Retenion
1.2kgf (MIN)

原材料:Matorial:

1. 塑胶:Housing:
Hing Temperature Thermaplastics,
U1 94V-0 LCP White/Black







2. 端子>Contact:Copper Alloy C5191

3. 外壳:Shell: Copper Alloy SUS304

电镀:Finish:

1. 端子>Contact: Plated Gold in Mating Area:
半金锡 1U

2. 外壳:Shell:
Nickel Plating



RECOMMENDED PCB LAYOUT
TOLERANCE:±0.05

		深圳市华德共创科技有限公司 Shenzhen Huade co-create Technology Co.,LTD 电话: 0755-27111216 传真: 0755-29940187			
-TOLERANCES- UNLESS OTHERWISE SPECIFIED 公差参数表			TITLE: MICRO四脚短脚卷边铜壳镀镍有柱 产品名称: 针长1.5		
X.X ±0.30	X.X* ±3°	APPD: 核准:	PART NO: 产品编号: MICRO-ZL-101PWB		
X.XX ±0.20	X.XX* ±2°	CHECK: 校对: 王建业	DATE	SCALE	UNIT
X.XXX ±0.10	X.XXX* ±1°	DRAW: 绘图: 黄艳兰	2016-03-12	1:1	mm
					CODE NUMBER A001