





SPECIFICATIONS
Current Rating: 3Amps
Insulation Resistance: 1000MΩ Min
Contact Resistance: 20mΩ Max
Withstanding Voltage: AC 1000V
Operation Temperature: -40° to +105°
Contact Material: Brass
Standard: PA6T
Insrlator Material: Polyester (UL 94V-0)
Contact Plating: Gold Flash
Max. Processing Temp: 240° C for 30-60 seconds
(260° C for 5 seconds)

P/N	PIN	DIM. A	DIM. B
HMT-PM254-2*01S-H85	1	0.00	2.54
HMT-PM254-2*02S-H85	2	2.54	5.08
HMT-PM254-2*03S-H85	3	5.08	7.62
HMT-PM254-2*04S-H85	4	7.62	10.16
HMT-PM254-2*05S-H85	5	10.16	12.70
HMT-PM254-2*06S-H85	6	12.70	15.24
HMT-PM254-2*07S-H85	7	15.24	17.78
HMT-PM254-2*08S-H85	8	17.78	20.32
HMT-PM254-2*09S-H85	9	20.32	22.86
.....			
HMT-PM254-2*40S-H85	40	(PIN-1) X 2.54	(PIN) X 2.54

GENERAL TOLERANCES UNLESS SPECIFIED		 深圳市华明通电子有限公司 HMTconn Shenzhen Huamingtong Electronics Co., Ltd		
X.±0.50	X.°±5°	PART NO.	TITLE: 2.54FH H8.5 2xnPin	
.X±0.20	.X°±2°	HMT-PM254-2*NS-H85	SMT U型 PC7.2 PB8.8 6T	
.XX±0.10	.XX°±1°	DESIGN: James	CUSTOMER	SIZE
MANUFACTURE DWG		CHED: Talen		A4
		APPD: Sophia		UNITS
				MM
				SCALE
				N:A
				SHEET
				1/1