




P/N	PIN	DIM. A	DIM. B
HMT-2.54-2*3P-NJ	2*3	5.08	26.92
HMT-2.54-2*4P-NJ	2*4	7.62	29.46
HMT-2.54-2*5P-NJ	2*5	10.16	32.00
HMT-2.54-2*6P-NJ	2*6	12.70	34.54
HMT-2.54-2*7P-NJ	2*7	15.24	37.08
HMT-2.54-2*8P-NJ	2*8	17.78	39.60
HMT-2.54-2*10P-NJ	2*10	22.86	44.70
HMT-2.54-2*12P-NJ	2*12	27.94	49.78
HMT-2.54-2*13P-NJ	2*13	30.48	52.30
HMT-2.54-2*15P-NJ	2*15	35.56	57.40
HMT-2.54-2*17P-NJ	2*17	40.64	62.50
HMT-2.54-2*20P-NJ	2*20	48.26	70.10
HMT-2.54-2*25P-NJ	2*25	60.96	82.85
HMT-2.54-2*30P-NJ	2*30	73.66	95.40
HMT-2.54-2*32P-NJ	2*32	78.74	100.48



GENERAL TOLERANCES UNLESS SPECIFIED		 深圳市华明通电子有限公司 Shenzhen Huamingtong Electronics Co., Ltd			
X. ±0.30	X.° ±5°	PART NO.	TITLE: 2.54DC2-NPin		
.X ±0.25	.X° ±1°	HMT-2.54-2*NP-NJ	H17 180度 PC3.8 PBT		
.XX ±0.20	.XX° ±0.5°	DESIGN: James	CUSTOMER	SIZE	
MANUFACTURE DWG		CHED: Talen		A4	UNITS
		APPD: Sophia		SCALE	SHEET
				N:A	1/1