





| 修<br>订    | 标<br>记 | 修<br>改<br>描<br>述 | 签<br>名 | 日<br>期     |
|-----------|--------|------------------|--------|------------|
| REV<br>NO |        | NEW DWG          |        | 2016-03-12 |
|           |        |                  |        |            |



#### NOTES:

- MATERIAL:
  - HOUSING: HALOGEN FREE THERMOPLASTIC, HIGH TEMP.UL94V-0; COLOR:NATURAL.
  - CONTACT: COPPER ALLOY
  - FITTING NAIL: COPPER ALLOY
- FINISH:
  - CONTACT & SOLDER:
    - 50~100u" NICKEL UNDER PLATING OVERALL
    - 3u" GOLD PLATING ON CONTACT
    - 80~150u" PURE-TIN PLATING OVERALL
  - GOLD FLASH ON CONTACT AND 80~150u"(MIN) MATT-TIN PLATING OVERALL
  - 15u" GOLD ON CONTACT AND 80~150u"(MIN) MATT-TIN PLATING OVERALL
- FITTING NAIL:
  - 50~100u" NICKEL UNDER PLATING OVERALL
  - 80~150u" MATT TIN PLATING OVERALL
- REFLOW SOLDER CAPABLE TO 260°C PER (pin)
- Working voltage less than 36 volts (per pin)
- Voltage: 50 Volts AC (per pin)
- HOUSING: NY9T



| CKT  | DIMA | DIMB | DIMC | DIMD | DIME  |
|------|------|------|------|------|-------|
| 2*3  | 6.0  | 2.0  | 4.5  | 3.8  | 4.43  |
| 2*4  | 7.0  | 3.0  | 5.5  | 4.8  | 5.43  |
| 2*5  | 8.0  | 4.0  | 6.5  | 5.8  | 6.43  |
| 2*6  | 9.0  | 5.0  | 7.5  | 6.8  | 7.43  |
| 2*7  | 10.0 | 6.0  | 8.5  | 7.8  | 8.43  |
| 2*8  | 11.0 | 7.0  | 9.5  | 8.8  | 9.43  |
| 2*9  | 12.0 | 8.0  | 10.5 | 9.8  | 10.43 |
| 2*10 | 13.0 | 9.0  | 11.5 | 10.8 | 11.43 |
| 2*11 | 14.0 | 10.0 | 12.5 | 11.8 | 12.43 |
| 2*12 | 15.0 | 11.0 | 13.5 | 12.8 | 13.43 |
| 2*15 | 18.0 | 14.0 | 16.5 | 15.8 | 16.43 |
| 2*20 | 23.0 | 19.0 | 21.5 | 20.8 | 21.43 |
| 2*25 | 28.0 | 24.0 | 26.5 | 25.8 | 26.43 |



深圳市华德共创科技有限公司

Shenzhen Huade co-create Technology Co.,LTD

电话：0755-27111216 传真：0755-29940187

-TOLERANCES-  
UNLESS OTHERWISE SPECIFIED  
公差参数表

|       |            |        |           |                   |                                 |                   |      |             |
|-------|------------|--------|-----------|-------------------|---------------------------------|-------------------|------|-------------|
| X.X   | $\pm 0.30$ | X.X*   | $\pm 3^*$ | APPD:<br>核准:      | TITLE:<br>产品名称: SHLD1.0双排带扣立贴针座 |                   |      |             |
| X.XX  | $\pm 0.20$ | X.XX*  | $\pm 2^*$ | CHECK:<br>校对: 王建业 | PART NO:<br>产品编号:               | HDGC1006WV-S-2XnP |      |             |
| X.XXX | $\pm 0.10$ | X.XXX* | $\pm 1^*$ | DRAW:<br>绘图: 黄艳兰  | DATE                            | SCALE             | UNIT | CODE NUMBER |
|       |            |        |           |                   | 2016-03-12                      | 1:1               | mm   | A001        |