









修订 REV	标记 MARK	修改摘要 REVISION DESCRIPTION	签名 SIGNATURE	日期 DATE
AO		NEW RELEASE	黄艳兰	2012-12-10



Recommended P.C.B Layout
General Tolerance±0.05



- 1.Material(Insulators):LP-LCP,UL94V-0
- 2.Color:Blank-Natural;BK-Black
- 3.Environmental protection Standard:Blank-Ordinary
RoHS;HF-Halogen Free
- 4.Material(Pin):PB-Phosphor Bronze
- 5.Plating :SN-Bright Tin Plated;AU-Gold flash;AU3-Gold 3U"
- 6.Package:Blank-Tape&Reel,SPQ:4.5K/reel preferred

Poles	Dimensions(mm)		Poles	Dimensions(mm)	
	A	B		A	B
02	0.60	3.00	12	6.60	9.00
03	1.20	3.60	13	7.20	9.60
04	1.80	4.20	14	7.80	10.20
05	2.40	4.80	15	8.40	10.80
06	3.00	5.40	16	9.00	11.40
07	3.60	6.00	17	9.60	12.00
08	4.20	6.60	18	10.20	12.60
09	4.80	7.20	19	10.80	13.20
10	5.40	7.80	20	11.40	13.80
11	6.00	8.40	22	12.60	14.40

■ Specification

- Voltage Rating : 30V AC/DC
- Current Rating : 0.2A AC/DC
- Withstanding Voltage : 200V AC /minute
- Insulation Resistance : ≥100MΩ
- Temperature Range : - 25°C to + 85°C
- Contact Resistance : ≤30mΩ
- After Environmental Testing: ≤40mΩ
- Suitable Wire/Cable:AWG #34 to #36,OD:0.32 to 0.29mm



深圳市华德共创科技有限公司

Shenzhen Huade co-create Technology Co.,LTD
TEL : 0755-27111216 FAX : 0755-29940187

-TOLERANCES- UNLESS OTHERWISE SPECIFIED 公差参数表				TITLE: 产品名称 : 0.6卧贴				
X.X	±0.30	X.X°	±3°	APPD: 核准 : 谢亮	PART NO: 产品编号 : HDGC0601WR-S-XP			
X.XX	±0.30	X.XX°	±2°	CHECK: 校对 : 王建业	DATE	SCALE	UNIT	CODE NUMBER
X.XXX	±0.10	X.XXX°	±1°	DRAW: 绘图 : 黄艳兰	2012-12-10	1:1	mm	A096