

## 74HC08D-HX/74HC08N-HX Quad 2-input and gates

### Description


The 74HC08D-HX/74HC08N-HX contains four independent 2-input AND gates, perform the Boolean function  $Y = A \cdot B$  or  $Y = A + B$  in positive logic.

- B or  $Y = A + B$  in positive logic.

### Features

- ★ Operation Voltage Range: 2~6V
- ★ Low Quiescent Current:  $I_{CC} = 2\mu A$  (Max)
- ★ High Speed:  $t_{PD} = 8ns$  (Typ)
- ★ Low Input Current: 100nA (Max)
- ★ ESD protection:
  - HBM: ANSI/ESDA/JEDEC JS-001 2023 exceeds 1000 V
  - CDM: ANSI/ESDA/JEDEC JS-002 2022 exceeds 2000 V
- ★ Latch-up performance  $\leq 250$  mA
- ★ Package Option: DIP-14 and SOP-14

### Pin Configuration



## Function Tables (Each Gate)

INPUT(A)	INPUT(B)	OUTPUT(Y)
H	H	H
H	L	L
L	H	L
L	L	L

## LOGIC DIAGRAM (Positive Logic)



## ABSOLUTE MAXIMUM RATING ( $T_A=25^{\circ}\text{C}$ , unless otherwise specified)

PARAMETER	SYMBOL	RATINGS	UNIT
Supply Voltage	$V_{CC}$	-0.5~7	V
Input Clamp Current	$I_{IK}$	$\pm 20$	mA
Output Clamp Current	$I_{OK}$	$\pm 20$	mA
Output Current	$I_{OUT}$	$\pm 25$	mA
VCC or GND Current	$I_{CC}$	$\pm 50$	mA
Storage Temperature	$T_{STG}$	-65 ~ +150	$^{\circ}\text{C}$

Note: Absolute maximum ratings are those values beyond which the device could be permanently damaged. Absolute maximum ratings are stress ratings only and functional device operation is not implied.

## Recommended Operating Conditions

PARAMETER	SYMBOL	TEST CONDITIONS	MIN	TYP	MAX	UNIT
Supply Voltage	$V_{CC}$	-	2	-	6	V
Input Voltage	$V_{IN}$	-	0	-	$V_{CC}$	V
Output Voltage	$V_{OUT}$	-	0	-	$V_{CC}$	V
Input Transition Rise or Fall Rate	$t_r, t_f$	$V_{CC}=2\text{V}$	-	-	1000	ns
		$V_{CC}=4.5\text{V}$	-	-	500	
		$V_{CC}=6\text{V}$	-	-	400	
Operating Temperature	$T_A$	-	-40	-	+125	$^{\circ}\text{C}$

## Thermal Data

PARAMETER	SYMBOL	RATINGS	UNIT
Junction to Ambient	DIP-14	100	$^{\circ}\text{C}/\text{W}$
	SOP-14	125	$^{\circ}\text{C}/\text{W}$

## Static Characteristics (TA=25°C ,unless otherwise specified)

PARAMETER	SYMBOL	TEST CONDITIONS	MIN	TYP	MAX	UNIT
High-Level Input Voltage	V <sub>IH</sub>	V <sub>CC</sub> =2V	1.5	-	-	V
		V <sub>CC</sub> =4.5V	3.15	-	-	
		V <sub>CC</sub> =6V	4.2	-	-	
Low-Level Input Voltage	V <sub>IL</sub>	V <sub>CC</sub> =2V	-	-	0.5	V
		V <sub>CC</sub> =4.5V	-	-	1.35	
		V <sub>CC</sub> =6V	-	-	1.8	
High-Level Output Voltage	V <sub>OH</sub>	V <sub>CC</sub> =2V, I <sub>OH</sub> =20μA	1.9	1.998	-	V
		V <sub>CC</sub> =4.5V, I <sub>OH</sub> =20μA	4.4	4.499	-	
		V <sub>CC</sub> =6V, I <sub>OH</sub> =20μA	5.9	5.999	-	
		V <sub>CC</sub> =4.5V, I <sub>OH</sub> =4mA	3.98	4.32	-	
		V <sub>CC</sub> =6V, I <sub>OH</sub> =5.2mA	5.48	5.81	-	
Low-Level Output Voltage	V <sub>OL</sub>	V <sub>CC</sub> =2V, I <sub>OL</sub> =20μA	-	0.002	0.1	V
		V <sub>CC</sub> =4.5V, I <sub>OL</sub> =20μA	-	0.001	0.1	
		V <sub>CC</sub> =6V, I <sub>OL</sub> =20μA	-	0.001	0.1	
		V <sub>CC</sub> =4.5V, I <sub>OL</sub> =4mA	-	0.15	0.26	
		V <sub>CC</sub> =6V, I <sub>OL</sub> =5.2mA	-	0.16	0.26	
Input Leakage Current	I <sub>I(LEAK)</sub>	V <sub>CC</sub> = 6V, V <sub>IN</sub> =V <sub>CC</sub> or GND	-	±0.1	±100	nA
Quiescent Supply Current	I <sub>Q</sub>	V <sub>CC</sub> =6V, V <sub>IN</sub> =V <sub>CC</sub> or GND, I <sub>OUT</sub> =0	-	-	8	μA
Input Capacitance	C <sub>IN</sub>	V <sub>CC</sub> =2V~6V	-	3	10	pF


## Dynamic Characteristics (TA=25OC, Input: tr=tf=6ns, unless otherwise specified )

PARAMETER	SYMBOL	TEST CONDITIONS	MIN	TYP	MAX	UNIT
Propagation delay from Input(A or B) to Output(Y)	t <sub>PLH</sub> , t <sub>PHL</sub>	V <sub>CC</sub> =2V, C <sub>L</sub> =50pF	-	25	90	ns
		V <sub>CC</sub> =4.5V, C <sub>L</sub> =50pF	-	9	18	
		V <sub>CC</sub> =6V, C <sub>L</sub> =50pF	-	7	15	
Output Transition Time	t <sub>T</sub>	V <sub>CC</sub> =2V	-	19	75	ns
		V <sub>CC</sub> =4.5V	-	7	15	
		V <sub>CC</sub> =6V	-	6	13	


## Operating Characteristics (TA=25OC, unless otherwise specified)

PARAMETER	SYMBOL	TEST CONDITION	RATINGS	UNIT
Power Dissipation Capacitance	C <sub>PD</sub>	No Load	20	pF

## Test Circuit and Waveforms





Note:  $C_L$  includes probe and jig capacitance.





## Package Information

74HC08N-HX DIP 14 package information







Symbol	Millimeter		
	Min	Nom	Max
A	3.20	3.30	3.40
b	0.44	----	0.53
b1	0.43	0.46	0.49
c	0.25	----	0.30
c1	0.24	0.25	0.26
D	18.95	19.05	19.15
E	6.25	6.35	6.45
e	2.54BSC		
eA	7.62	-----	9.50
L	3.00	----	----



SECTION B-B

### 74HC08D-HX SOP 14 package information



SYMBOL	MILLIMETER		
	MIN	NOM	MAX
A	--	--	1.70
A1	0.10	0.15	0.21
A2	1.40	1.45	1.50
A3	0.60	0.65	0.70
b	0.33	--	0.47
b1	0.32	0.41	0.44
c	0.20	--	0.24
c1	0.19	0.20	0.21
D	8.45	8.60	8.75
E	5.80	6.00	6.20
E1	3.85	3.90	4.00
e	1.27(BSC)		
L	0.50	0.60	0.70
L1	1.10(BSC)		
$\theta 1$	8°	~	15°
$\theta 2$	8°	~	15°
$\theta 3$	8°	~	15°
$\theta 4$	8°	~	15°
$\theta 5$	0°	~	6°