

General Description

This MOSFET uses advanced trench technology to provide excellent $R_{DS(ON)}$, low gate charge and operation with gate voltages as low as 2.5V. This device is suitable for use as a battery protection or in other switching application.

Features

- Low gate charge
- High power and current handing capability
- Lead free product is acquired

Applications

- Load switch
- Battery protection
- Power management




Key Performance Parameters

Parameter	Value	Unit
V_{DS}	-50	V
$R_{DS(ON), max} @ V_{GS}=10\text{ V}$	5.9	Ω

Marking Information

Product Name	Package	Marking
BSS84K	SOT-23	84K

Package & Pin information



Absolute Maximum Ratings at $T_j=25^{\circ}\text{C}$ unless otherwise noted

Parameter	Symbol	Value	Unit
Drain-source voltage	V_{DS}	-50	V
Gate-source voltage	V_{GS}	± 20	V
Continuous Drain Current	I_D	-0.2	A
Pulsed Drain Current ¹⁾	$I_{D,pulse}$	-0.8	A
Power Dissipation	P_D	357	W
Operation and storage temperature	T_{stg}, T_j	-55 to 150	$^{\circ}\text{C}$

Thermal Characteristics

Parameter	Symbol	Value	Unit
Thermal resistance, junction-to-Ambient	$R_{\theta JA}$	350	$^{\circ}\text{C/W}$

Electrical Characteristics at $T_j=25^{\circ}\text{C}$ unless otherwise specified

Parameter	Symbol	Min.	Typ.	Max.	Unit	Test condition
Drain-source breakdown voltage	BV_{DSS}	-50			V	$V_{GS}=0\text{ V}, I_D=250\text{ }\mu\text{A}$
Gate threshold voltage	$V_{GS(th)}$	-1		-2.5	V	$V_{DS}=V_{GS}, I_D=250\text{ }\mu\text{A}$
Drain-source on-state resistance	$R_{DS(ON)}$		4.9	5.9	Ω	$V_{GS}=-10\text{ V}, I_D=-0.5\text{ A}$
Drain-source on-state resistance	$R_{DS(ON)}$		5.3	6.9	Ω	$V_{GS}=-4.5\text{ V}, I_D=-0.25\text{ A}$
Gate-source leakage current	I_{GSS}			10	μA	$V_{GS}=20\text{ V}, V_{DS}=0\text{ V}$
				-10		$V_{GS}=-20\text{ V}, V_{DS}=0\text{ V}$
Drain-source leakage current	I_{DSS}			-1	μA	$V_{DS}=-60\text{ V}, V_{GS}=0\text{ V}$

Dynamic Characteristics

Parameter	Symbol	Min.	Typ.	Max.	Unit	Test condition
Input capacitance	C_{iss}		23.5		pF	$V_{GS}=0\text{ V}$, $V_{DS}=-25\text{ V}$, $f=1.0\text{ MHz}$
Output capacitance	C_{oss}		10.6		pF	
Reverse transfer capacitance	C_{rss}		4.9		pF	
Turn-on Delay Time	$t_{d(on)}$		2.1		ns	$V_{GS}=-10\text{ V}$, $V_{DD}=-30\text{ V}$, $I_D=-0.2\text{ A}$, $R_{GEN}=3\ \Omega$
Turn-on Rise Time	t_r		2.41		ns	
Turn-Off Delay Time	$t_{d(off)}$		29.9		ns	
Turn-Off Fall Time	t_f		16.3		ns	

Gate Charge Characteristics

Parameter	Symbol	Min.	Typ.	Max.	Unit	Test condition
Total Gate Charge	Q_g		0.75		nC	$V_{GS}=-10\text{ V}$, $V_{DS}=-30\text{ V}$, $I_D=-0.2\text{ A}$
Gate-Source Charge	Q_{gs}		0.15		nC	
Gate-Drain Charge	Q_{gd}		0.11		nC	

Body Diode Characteristics

Parameter	Symbol	Min.	Typ.	Max.	Unit	Test condition
Source drain current (Body Diode)	I_{SD}			-0.2	A	$T_A=25^\circ\text{C}$
Diode forward voltage ²⁾	V_{SD}		-0.9	-1.2	V	$I_S=-0.2\text{ A}$, $V_{GS}=0\text{ V}$

Note: 1) Pulse width limited by maximum allowable junction temperature.

2) Repetitive Rating: Pulse width limited by maximum junction temperature.

Electrical Characteristics Diagrams




Figure 1. Typ. output characteristics




Figure 2. Typ. transfer characteristics




Figure 3. Typ. capacitances




Figure 4. Gate charge




Figure 5. Body-diode characteristics





Figure 6. $R_{DS(ON)}$ vs junction temperature

Package Information



Symbol	mm	
	Min	Max
A	0.900	1.150
A1	0.000	0.100
A2	0.900	1.050
b	0.300	0.500
c	0.080	0.150
D	2.800	3.000
E	1.200	1.400
e	0.950 TYP	
e1	1.800	2.000
L	0.550 REF	
L1	0.300	0.500
θ	0°	8°

Version : SOT-23-V package outline dimension

Ordering Information

Package Type	Units/ Reel	Reels/ Inner Box	Units/ Inner Box	Inner Boxes/ Carton Box	Units/ Carton Box
SOT-23	3000	15	45000	4	180000

Legal Disclaimer

The information given in this document shall in no event be regarded as a guarantee of conditions or characteristics. With respect to any examples or hints given herein, any typical values stated herein and/or any information regarding the application of the device, Oriental Semiconductor hereby disclaims any and all warranties and liabilities of any kind, including without limitation, warranties of non-infringement of intellectual property rights of any third party.

For further information on technology, delivery terms and conditions and prices, please contact the Oriental Semiconductor sales representatives (www.orientalsemi.com).

© Oriental Semiconductor Co.,Ltd. All Rights Reserved 