

SOT-23 Plastic-Encapsulate MOSFETS

Features

- $V_{DS} = -60V$
- $I_D = -2A$
- $R_{DS(on)}@V_{GS} = -10V < 220m\Omega$
- $R_{DS(on)}@V_{GS} = -4.5V < 270m\Omega$
- Trench MOSFET technology
- Voltage controlled small signal switch
- Fast Switching Speed

Applications

- Battery operated systems
- Solid-state relays
- Direct logic-level interface: TTL/CMOS




Mechanical Data

- Case: SOT-23
Molding compound meets UL 94V-0 flammability rating, RoHS-compliant, halogen-free
- Terminals: Solder plated, solderable per MIL-STD-750, Method 2026

Reference News

Drain-source Voltage
-60 V

Drain Current
-2 Ampere



Maximum Ratings (Ta=25°C Unless otherwise specified)

| PARAMETER | SYMBOL | UNIT | VALUE |
|---|-----------------|--------|------------|
| Drain-source Voltage | V_{DS} | V | -60 |
| Gate-source Voltage | V_{GS} | V | ± 20 |
| Drain Current ⁽¹⁾⁽²⁾ | I_D | A | -2.0 |
| T _A =25°C @ Steady State | | | |
| Pulsed Drain Current | I_{DM} | A | -8.0 |
| Total Power Dissipation @ T _A =25°C | P_D | W | 1.5 |
| Thermal Resistance Junction-to-Ambient @ Steady State | $R_{\theta JA}$ | °C / W | 83 |
| Junction and Storage Temperature Range | T_J, T_{STG} | °C | -55 ~ +150 |

Ordering Information

| PACKAGE | PACKAGE CODE | UNIT WEIGHT(g) | REEL(pcs) | BOX(pcs) | CARTON(pcs) | DELIVERY MODE |
|---------|--------------|----------------|-----------|----------|-------------|---------------|
| SOT-23 | R1 | 0.008 | 3000 | 30000 | 120000 | 7" |

● **Static Parameter Characteristics** (Ta=25°C Unless otherwise specified)

| PARAMETER | SYMBOL | Condition | UNIT | Min | Typ | Max |
|---------------------------------------|--------------|--------------------------------|------------|------|-------|-----------|
| Drain-Source Breakdown Voltage | BV_{DSS} | $V_{GS}=0V, I_D=-250\mu A$ | V | -60 | — | — |
| Zero Gate Voltage Drain Current | I_{DSS} | $V_{DS}=-60V, V_{GS}=0V$ | μA | — | — | -1.0 |
| Gate-Body Leakage Current | I_{GSS} | $V_{GS}=\pm 20V, V_{DS}=0V$ | nA | — | — | ± 100 |
| Gate Threshold Voltage | $V_{GS(th)}$ | $V_{DS}=V_{GS}, I_D=-250\mu A$ | V | -1.0 | -1.65 | -2.5 |
| Static Drain-Source On-Resistance | $R_{DS(on)}$ | $V_{GS}=-10V, I_D=-1.25A$ | m Ω | — | 170 | 220 |
| | | $V_{GS}=-4.5V, I_D=-1.0A$ | | — | 185 | 270 |
| Diode Forward Voltage | V_{SD} | $I_S=-2A, V_{GS}=0V$ | V | — | — | -1.2 |
| Maximum Body-Diode Continuous Current | I_S | — | A | — | — | -2 |

● **Dynamic Parameters** (Ta=25°C Unless otherwise specified)

| PARAMETER | SYMBOL | Condition | UNIT | Min | Typ | Max |
|------------------------------|-----------|--|------|-----|-----|-----|
| Input Capacitance | C_{iss} | $V_{DS}=-30V$ $V_{GS}=0V$ $f=1MHz$ | pF | — | 495 | — |
| Output Capacitance | C_{oss} | | | — | 41 | — |
| Reverse Transfer Capacitance | C_{rss} | | | — | 26 | — |

● **Switching Parameters** (Ta=25°C Unless otherwise specified)

| PARAMETER | SYMBOL | Condition | UNIT | Min | Typ | Max |
|---------------------|--------------|--|------|-----|-----|-----|
| Total Gate Charge | Q_g | $V_{GS}=-10V$ $V_{DS}=-30V$ $I_D=-1.5A$ | nC | — | 11 | — |
| Gate-Source Charge | Q_{gs} | | | — | 3 | — |
| Gate-Drain Charge | Q_{gd} | | | — | 2 | — |
| Turn-on Delay Time | $t_{D(on)}$ | $V_{GS}=-10V, V_{DS}=-30V, R_{GEN}=3.0\Omega$ $I_D=-1.5A$ | ns | — | 40 | — |
| Turn-on Rise Time | t_r | | | — | 35 | — |
| Turn-off Delay Time | $t_{D(off)}$ | | | — | 15 | — |
| Turn-off fall Time | t_f | | | — | 10 | — |

● Package Outline Dimensions (SOT-23)

| Symbol | Dimensions | | | |
|----------|-------------|------|----------|-------|
| | Millimeters | | Inches | |
| | Min. | Max. | Min. | Max. |
| A | 0.90 | 1.15 | 0.035 | 0.045 |
| A1 | - | 0.10 | - | 0.004 |
| A2 | 0.90 | 1.05 | 0.035 | 0.041 |
| b | 0.30 | 0.50 | 0.012 | 0.020 |
| c | 0.10 | 0.20 | 0.004 | 0.008 |
| D | 2.80 | 3.00 | 0.110 | 0.118 |
| E | 1.20 | 1.40 | 0.047 | 0.055 |
| E1 | 2.25 | 2.55 | 0.089 | 0.100 |
| e | 0.950TYP | | 0.037TYP | |
| e1 | 1.80 | 2.00 | 0.071 | 0.079 |
| L | 0.550REF | | 0.022REF | |
| L1 | 0.30 | 0.50 | 0.012 | 0.020 |
| θ | - | 8° | - | 8° |

● Suggested Pad Layout

| Symbol | Dimensions | | | |
|--------|-------------|------|--------|-------|
| | Millimeters | | Inches | |
| | Min. | Max. | Min. | Max. |
| J | 0.80 | - | 0.031 | - |
| K | - | 0.90 | - | 0.035 |
| M | 2.00 | - | 0.078 | - |
| N | - | 1.90 | - | 0.074 |