




REV.	DESCRIPTION	ECN NO.	NAME	DATE


Part No	Pin	A	B	C
AF-GH1.25-2PWT-W1	2	1.25	5.75	3.75
AF-GH1.25-3PWT-W1	3	2.50	7.00	5.00
AF-GH1.25-4PWT-W1	4	3.75	8.25	6.25
AF-GH1.25-5PWT-W1	5	5.00	9.50	7.50
AF-GH1.25-6PWT-W1	6	6.25	10.75	8.75
AF-GH1.25-7PWT-W1	7	7.50	12.00	10.00
AF-GH1.25-8PWT-W1	8	8.75	13.25	11.25
AF-GH1.25-9PWT-W1	9	10.00	14.50	12.50
AF-GH1.25-10PWT-W1	10	11.25	15.75	13.75
AF-GH1.25-11PWT-W1	11	12.50	17.00	15.00
AF-GH1.25-12PWT-W1	12	13.75	18.25	16.25
AF-GH1.25-13PWT-W1	13	15.00	19.50	17.50
AF-GH1.25-14PWT-W1	14	16.25	20.75	18.75
AF-GH1.25-15PWT-W1	15	17.50	22.00	20.00
AF-GH1.25-16PWT-W1	16	18.75	23.25	21.25

NOTES:

- 1. BASE: LCP
- 2. PIN: Brass
- 3. Solder Tab: Brass

SPECIFICATIONS:

- 1. Spacing: 1.25
- 2. Voltage Rating: 125V AC DC
- 3. Current Rating: 1A AC, DC
- 4. Insulation Resistance: 100MΩ Min
- 5. Contact Resistance: 20mΩ Max
- 6. Withstanding voltage: 500V AC 1/Minute
- 7. Temperature Range: $-25^{\circ}\text{C} \sim +85^{\circ}\text{C}$

GENERAL TOLERANCE		DONGGUAN BAOXUN PRECISION TECHNOLOGY CO., LTD		BXCONN[®] 	
DIM. x. ±0.20 x.x ±0.10 x.xx ±0.05		TITLE: WAFER GH1.25 卧贴带扣			
GENERAL ANGLE: x.' ±5° x.x' ±3° x.xx' ±1°		DWG. NO.: AF-GH1.25-NPWT-W1 CHECKED: MAX			
		PART NO.: AF-GH1.25-NPWT-W1 DRAWN: ELLA			
UNIT: mm	SCALE: none	SHEET: 1 of 1	DWG. SIZE: A4	LAYER: bxconn	APPROVED: WILL