

[illegible]

REV.		DESCRIPTION	ECN NO.	NAME	DATE

Part No	Pin	A	B	C	D
AF-HY2.0-2PLT-W1	2	2.00	8.00	2.50	4.90
AF-HY2.0-3PLT-W1	3	4.00	10.00	2.50	6.90
AF-HY2.0-4PLT-W1	4	6.00	12.00	5.00	8.90
AF-HY2.0-5PLT-W1	5	8.00	14.00	7.00	10.90
AF-HY2.0-6PLT-W1	6	10.00	16.00	9.00	12.90
AF-HY2.0-7PLT-W1	7	12.00	18.00	11.00	14.90
AF-HY2.0-8PLT-W1	8	14.00	20.00	13.00	16.90
AF-HY2.0-9PLT-W1	9	16.00	22.00	15.00	18.90
AF-HY2.0-10PLT-W1	10	18.00	24.00	17.00	20.90
AF-HY2.0-11PLT-W1	11	20.00	26.00	19.00	22.90
AF-HY2.0-12PLT-W1	12	22.00	28.00	21.00	24.90
AF-HY2.0-13PLT-W1	13	24.00	30.00	23.00	26.90
AF-HY2.0-14PLT-W1	14	26.00	32.00	25.00	28.90
AF-HY2.0-15PLT-W1	15	28.00	34.00	27.00	30.90
AF-HY2.0-16PLT-W1	16	30.00	36.00	29.00	32.90

NOTES:

1.BASE: LCP

2.PIN: Brass

3.Solder Tab: Brass

SPECIFICATIONS:

1.Spacing: 2.0

2.Voltage Rating: 250V AC DC

3.Current Rating: 2A AC DC


4.Insulation Resistance: 800MΩ Min

5.Contact Resistance: 20mΩ Max

6.Withstanding voltage: 500V AC 1/Minute

7.Temperatuer Range: -25℃ ~+ 85℃

GENERAL TOLERANCE		DONGGUAN BAOXUN PRECISION TECHNOLOGY CO., LTD				
DIM.	TOL.	TITLE: WAFER 2.00 立贴带扣				
x.	±0.20	DWG. NO.: AF-HY2.0-NPLT-W1		CHECKED: MAX		
x.x	±0.10	PART NO.: AF-HY2.0-NPLT-W1		DRAWN: ELLA		
x.xx	±0.05	UNIT: mm		SCALE: none	SHEET: 1 of 1	
GENERAL ANGLE:		DWG. SIZE: A4		LAYER: bxconn	APPROVED: WILL	
x.°	±5°					
x.x°	±3°					
x.xx°	±1°					

[illegible]