


### Features

Bi-directional ESD protection of one line  
Reverse stand-off voltage: 24V  
Low reverse clamping voltage  
Low leakage current  
Fast response time  
IEC 61000-4-2 (ESD) immunity test :  
Air discharge: ±30kV  
Contact discharge: ±30kV

### Applications

Computers and peripherals  
High speed data lines  
Audio and video equipment  
Cellular handsets and accessories  
Subscriber identity module(SIM) card protection  
Portable electronics  
FireWire  
Other electronics equipments communi- cation systems

24M



### Absolute Maximum Rating


Parameter	Symbol	Value	Unit
Peak Pulse Power (8/20μs)	Ppk	350	W
Peak Pulse Current (8/20μs)	IPP	7	A
ESD per IEC 61000-4-2 (Air)	VESD	±30	kV
ESD per IEC 61000-4-2 (Contact)		±30	
Operating Temperature Range	TJ	-55to +125	°C
Storage Temperature Range	Tstg	-55 to +150	°C

## Electrical Characteristics





Parameter	Symbol	Test Condition	Min	Typ	Max	Unit
Reverse Working Voltage	$V_{RWM}$				24	V
Breakdown Voltage	$V_{BR}$	$I_T = 1mA$	27.2		30.2	V
Reverse Leakage Current	$I_R$	$V_{RWM} = \pm 24V$			0.1	$\mu A$
Clamping Voltage	$V_C$	$I_{PP} = 7A$ (8 x 20 $\mu s$ pulse)			50	V
Junction Capacitance	$C_j$	$V_R = 0V, f = 1MHz$			25	pF

## Electronics Parameter



Symbol	Parameter
$I_T$	Test Current
$I_{PP}$	Maximum Reverse Peak Pulse Current
$V_C$	Clamping Voltage @ $I_C$
$V_{BR}$	Breakdown Voltage @ $I_T$
$I_R$	Reverse Leakage Current @ $V_{RWM}$
$V_{RWM}$	Reverse Standoff Voltage



**RATING AND CHARACTERISTIC CURVES**



ESD pulse waveform according to IEC61000-4-2



8/20μs pulse waveform according to IEC 61000-4-



**Soldering parameters**

Reflow Condition		Pb-Free assembly (see as below)
Pre Heat	-Temperature Min ( $T_{s(min)}$ )	+150 °C
	-Temperature Max( $T_{s(max)}$ )	+200 °C
	-Time (Min to Max) (ts)	60-180 secs.
Average ramp up rate (Liquid us Temp ( $T_L$ ) to peak)		3 °C/sec. Max
$T_{s(max)}$ to $T_L$ - Ramp-up Rate		3 °C/sec. Max
Reflow	-Temperature( $T_L$ )(Liquid us)	+217 °C
	-Temperature( $t_L$ )	60-150 secs.
Peak Temp ( $T_P$ )		+260(+0/-5) °C
Time within 5 °C of actual Peak Temp ( $t_p$ )		30 secs. Max
Ramp-down Rate		6 °C/sec. Max
Time 25 °C to Peak Temp ( $T_P$ )		8 min. Max
Do not exceed		+260 °C



**Package Dimensions & Suggested Pad Layout**

**SOT23**




**SOT-23 mechanical data**

UNIT	A	C	D	E	HE	e	M	L	L1	a	
mm	max	1.1	0.15	1.4	3.0	2.6	0.5	1.95	0.55 (ref)	0.36 (ref)	0.0
	min	0.9	0.08	1.2	2.8	2.2	0.3	1.7			0.15
mil	max	43	6	55	118	102	20	77	22 (ref)	14 (ref)	0.0
	min	35	3	47	110	87	12	67			6

Dimensions	SOT23
<b>Z</b>	2.9
<b>X</b>	0.8
<b>Y</b>	0.9
<b>C</b>	2.0
<b>E</b>	1.35


Tape & reel specification

Tape



Symbol	Dimension (mm)
P0	4.00±0.10
P1	4.00±0.10
P2	2.00±0.10
D0	1.55±0.10
D1	1.05±0.10
E	1.55±0.10
F	3.60±0.10
W	8.00±0.10
A0	3.80±0.20
B0	3.25±0.20
K0	1.45±0.10
T	0.25±0.05
D2	178.0±3.0
D3	55Min.
D4	R24.0±3.0
G	R82.0±3.0
I	13.0±2.0
W1	11.0±3.0

7" Reel



Quantity: 3000PCS