




SPECIFICATIONS

Current Rating: 3Amps
Insulation Resistance: 1000MΩ Min
Contact Resistance: 20mΩ Max
Withstanding Voltage: AC 1000V
Operation Temperature: -40° to +105°
Contact Material: Brass
Standard: PA6T
Insulator Material: Polyester (UL 94V-0)
Contact Plating: Gold Flash
Max. Processing Temp: 240°C for 30-60 seconds
(260°C for 5 seconds)

P/N	PIN	DIM.A	DIM.B
AZ-PZ2.54-V12-2*1P	2*1	0.00	2.54
AZ-PZ2.54-V12-2*2P	2*2	2.54	5.08
AZ-PZ2.54-V12-2*3P	2*3	5.08	7.62
AZ-PZ2.54-V12-2*4P	2*4	7.62	10.16
AZ-PZ2.54-V12-2*5P	2*5	10.16	12.70
AZ-PZ2.54-V12-2*6P	2*6	12.70	15.24
AZ-PZ2.54-V12-2*7P	2*7	15.24	17.78
AZ-PZ2.54-V12-2*8P	2*8	17.78	20.32
AZ-PZ2.54-V12-2*9P	2*9	20.32	22.86
.....			
AZ-PZ2.54-V12-2*40P	2*40	(PIN-1)X2.54	(PIN)X2.54

GENERAL TOLERANCE		DONGGUAN BAOXUN PRECISION TECHNOLOGY CO., LTD				BXCONN [®]		
DIM.	TOL.	TITLE: 2.54PH H2.5 2xnPin 90度 PC3.0						
x.	±0.30	PA6.0 PB6.9 L13.8/18.8 6T 弯凹面						
x.x	±0.20	DWG. NO.: AZ-PZ2.54-V12-2*NP						CHECKED: MAX
x.xx	±0.10	PART NO.: AZ-PZ2.54-V12-2*NP						DRAWN: ELLA
GENERAL ANGLE:		UNIT: mm						APPROVED: WILL
x.°	±5°	SCALE:	SHEET:	DWG. SIZE:	LAYER:			
x.x°	±1°	none	1 of 1	A4	bxconn			
x.xx°	±0.5°							
