

FEATURES

Low Gate Charge
High Power and current handling capability
Lead free product is acquired

V_{DSS} 60 V
 I_D 3 A
 $R_{DS(ON)}$ 75 m Ω

APPLICATION


PWM Applications
Load Switch
Power Management

3422



SOT23-3L top view

Equivalent Circuit



MAXIMUM RATINGS AND ELECTRICAL CHARACTERISTICS

Absolute Maximum Ratings $T_c=25^\circ\text{C}$ unless otherwise noted

Symbol	Parameter	Limit	Unit
V_{DS}	Drain-Source Voltage ($V_{GS}=0V$)	60	V
V_{GS}	Gate-Source Voltage ($V_{DS}=0V$)	± 20	V
I_D	Drain Current-Continuous($T_A=25^\circ\text{C}$)	3	A
	Drain Current-Continuous($T_A=100^\circ\text{C}$)	1.9	A
I_{DM} (pluse)	Drain Current-Continuous@ Current-Pulsed (Note 1)	12	A
P_D	Maximum Power Dissipation($T_A=25^\circ\text{C}$)	1.5	W
	Maximum Power Dissipation($T_A=100^\circ\text{C}$)	0.6	W
E_{AS}	Avalanche energy (Note 2)	12	mJ
T_J, T_{STG}	Operating Junction and Storage Temperature Range	-55 To 150	$^\circ\text{C}$

Thermal Characteristic

Symbol	Parameter	Typ	Max	Unit
$R_{\theta JA}$	Thermal Resistance, Junction-to-Ambient		83	$^\circ\text{C/W}$

Electrical Characteristics $T_J=25^\circ\text{C}$ unless otherwise noted

Symbol	Parameter	Conditions	Min	Typ	Max	Unit
On/Off States						
BV_{DSS}	Drain-Source Breakdown Voltage	$V_{GS}=0V, I_D=250\mu A$	60			V
I_{DSS}	Zero Gate Voltage Drain Current	$V_{DS}=60V, V_{GS}=0V, T_J=25^\circ\text{C}$			1	μA
		$V_{DS}=60V, V_{GS}=0V, T_J=125^\circ\text{C}$			100	μA
I_{GSS}	Gate-Body Leakage Current	$V_{GS}=\pm 20V, V_{DS}=0V$			± 100	nA
$V_{GS(th)}$	Gate Threshold Voltage	$V_{DS}=V_{GS}, I_D=250\mu A$	1		2.5	V
g_{FS}	Forward Transconductance	$V_{DS}=5V, I_D=2A$		4.1		S
$R_{DS(ON)}$	Drain-Source On-State Resistance	$V_{GS}=10V, I_D=2A, T_J=25^\circ\text{C}$		75	85	m Ω
$R_{DS(ON)}$	Drain-Source On-State Resistance	$V_{GS}=4.5V, I_D=1.5A, T_J=25^\circ\text{C}$		90	100	m Ω
Dynamic Characteristics						
C_{iss}	Input Capacitance	$V_{DS}=30V, V_{GS}=0V, f=1.0\text{MHz}$		369		pF
C_{oss}	Output Capacitance			28		pF
C_{rss}	Reverse Transfer Capacitance			22		pF
R_g	Gate resistance	$V_{GS}=0V, V_{DS}=0V, f=1.0\text{MHz}$		0.78		Ω
Switching Parameters						
$t_{d(on)}$	Turn-on Delay Time	$V_{GS}=10V, V_{DS}=30V, R_L=15\Omega, R_{GEN}=3\Omega$		5		nS
t_r	Turn-on Rise Time			8		nS
$t_{d(off)}$	Turn-Off Delay Time			36		nS
t_f	Turn-Off Fall Time			21		nS
Q_g	Total Gate Charge	$V_{GS}=10V, V_{DS}=30V, I_D=2A$		9		nC
Q_{gs}	Gate-Source Charge			1.6		nC
Q_{gd}	Gate-Drain Charge			2		nC
Source-Drain Diode Characteristics						
I_{SD}	Source-Drain Current (Body Diode)				3	A
V_{SD}	Forward on Voltage (Note 3)	$V_{GS}=0V, I_S=2A$			1.2	V
t_{rr}	Reverse Recovery Time	$I_F=2A, dI/dt=100A/\mu s$		20		ns
Q_{rr}	Reverse Recovery Charge	$I_F=2A, dI/dt=100A/\mu s$		8		nC

Notes 1.Repetitive Rating: Pulse width limited by maximum junction temperature.

Notes 2.EAS condition: $T_J=25^\circ\text{C}, V_{DD}=40V, V_G=10V, R_g=25\Omega, L=0.5\text{mH}$.

Notes 3.Repetitive Rating: Pulse width limited by maximum junction temperature.

RATING AND CHARACTERISTIC CURVES




Figure 3. Power Dissipation




Figure 4. Drain Current




Figure 5. BV_{DS} vs Junction Temperature






Figure 6. $R_{DS(ON)}$ vs Junction Temperature



RATING AND CHARACTERISTIC CURVES

Figure 7. Gate Charge Waveforms




Figure 8. Capacitance




Figure 9. Body-Diode Characteristics





Figure 10. Maximum Safe Operating Area





Soldering parameters

Reflow Condition		Pb-Free assembly (see as below)
Pre Heat	-Temperature Min ($T_{s(min)}$)	+150 °C
	-Temperature Max ($T_{s(max)}$)	+200 °C
	-Time (Min to Max) (ts)	60-180 secs.
Average ramp up rate (Liquid us Temp (T_L) to peak)		3 °C/sec. Max
$T_{s(max)}$ to T_L - Ramp-up Rate		3 °C/sec. Max
Reflow	-Temperature (T_L) (Liquid us)	+217 °C
	-Temperature (t_L)	60-150 secs.
Peak Temp (T_P)		+260(+0/-5) °C
Time within 5 °C of actual Peak Temp (t_p)		30 secs. Max
Ramp-down Rate		6 °C/sec. Max
Time 25 °C to Peak Temp (T_P)		8 min. Max
Do not exceed		+260 °C



Package Dimensions & Suggested Pad Layout

SOT23



SOT-23 mechanical data

UNIT	A	C	D	E	H_E	e	M	L	L_1	a	
mm	max	1.1	0.15	1.4	3.0	2.6	0.5	1.95	0.55 (ref)	0.36 (ref)	0.0
	min	0.9	0.08	1.2	2.8	2.2	0.3	1.7			0.15
mil	max	43	6	55	118	102	20	77	22 (ref)	14 (ref)	0.0
	min	35	3	47	110	87	12	67			6

Dimensions	SOT23
Z	2.9
X	0.8
Y	0.9
C	2.0
E	1.35

Tape & reel specification

Tape		Symbol	Dimension (mm)
		P0	4.00±0.10
		P1	4.00±0.10
		P2	2.00±0.10
		D0	1.55±0.10
		D1	1.05±0.10
		E	1.55±0.10
		F	3.60±0.10
		W	8.00±0.10
		A0	3.80±0.20
		B0	3.25±0.20
		K0	1.45±0.10
		T	0.25±0.05
		D2	178.0±3.0
		D3	55Min.
		D4	R24.0±3.0
G	R82.0±3.0		
I	13.0±2.0		
W1	11.0±3.0		
Quantity: 3000PCS			

7" Reel

