










序号	品名	材质	制图 DRAWN	内容 DESCRIPTION	日期 DATE	GENERAL TOLERANCE		制图 DRAWING	EMMA			料号 PART NO.	BX-0.5FPC-2H-HFNP		版本 REV.	A			
						X±0.15	±1°	审核 CHECK	EVA	品名 TITLE	0.5-G前插后压(H:2.0)	页次 SHEET	1/2						
														.X±0.10	客户料号 CUTM.NO.				
																	.XX±0.05	批准 APPROVAL	JADE
1		2		3		4		5		6		7		8		9			

技术指标:

1. 额定电流: 0.5A
2. 温度范围: $-40\sim 85^{\circ}\text{C}$
3. 额定电压: 50V, AC/DC (等效)
4. 接触电阻: $\leq 0.03\Omega$
5. 绝缘电阻: $\geq 500\text{M}\Omega$



Part No	Pin	A	B	C	D	E
BX-0.5FPC-2H-HF40P	40	19.50	20.52	23.45	23.25	0.18
BX-0.5FPC-2H-HF41P	41	20.00	21.02	23.95	23.75	
BX-0.5FPC-2H-HF42P	42	20.50	21.52	24.45	24.25	
BX-0.5FPC-2H-HF43P	43	21.00	22.02	24.95	24.75	
BX-0.5FPC-2H-HF44P	44	21.50	22.52	25.45	25.25	
BX-0.5FPC-2H-HF45P	45	22.00	23.02	25.95	25.75	
BX-0.5FPC-2H-HF46P	46	22.50	23.52	26.45	26.25	
BX-0.5FPC-2H-HF47P	47	23.00	24.02	26.95	26.75	
BX-0.5FPC-2H-HF48P	48	23.50	24.52	27.45	27.25	
BX-0.5FPC-2H-HF49P	49	24.00	25.02	27.95	27.75	
BX-0.5FPC-2H-HF50P	50	24.50	25.52	28.45	28.25	0.20
BX-0.5FPC-2H-HF51P	51	25.00	26.02	28.95	28.75	
BX-0.5FPC-2H-HF52P	52	25.50	26.52	29.45	29.25	
BX-0.5FPC-2H-HF53P	53	26.00	27.02	29.95	29.75	
BX-0.5FPC-2H-HF54P	54	26.50	27.52	30.45	30.25	
BX-0.5FPC-2H-HF55P	55	27.00	28.02	30.95	30.75	
BX-0.5FPC-2H-HF56P	56	27.50	28.52	31.45	31.25	
BX-0.5FPC-2H-HF57P	57	28.00	29.02	31.95	31.75	
BX-0.5FPC-2H-HF58P	58	28.50	29.52	32.45	32.25	
BX-0.5FPC-2H-HF59P	59	29.00	30.02	32.95	32.75	
BX-0.5FPC-2H-HF60P	60	29.50	30.52	33.45	33.25	



序号	品名	材质	制图 DRAWN	变更内容 DESCRIPTION	日期 DATE	GENERAL TOLERANCE		制图 DRAWING	EMMA		料号 PART NO.	BX-0.5FPC-2H-HFNP	版本 REV.	A
1	端子	磷青铜/表面镀锡				X ± 0.15	$\pm 1^{\circ}$	审核 CHECK	EVA		品名 TITLE	0.5-G前插后压(H:2.0)	页次 SHEET	2/2
2	焊片	磷青铜/表面镀锡				.X ± 0.10		核准 APPROVAL	JADE		客户料号 CUTM.NO.			
3	基座	LCP UL94V-0 本色				.XX ± 0.05								
4	锁条	LCP UL94V-0 黑色						单位 UNITS	MM	比例 SCALE	1:1	Bossie (博锡)		