

# 产品规格书

# Product Specification

CUSTOMER 客户: \_\_\_\_\_

CUSTOMER PN 客户 PN: \_\_\_\_\_

HANG CRYSTAL P/N 杭晶物料编码: 5236H5-10.000N50DTVAL

MODEL 产品型号: OCXO 36x27, CMOS/TTL, 5.0V

NOMINAL FREQUENCY 频率: 10.000MHz

ISSUE DATE 日期: 2023 / 06 / 13

**CUSTOMER'S APPROVAL**

客户确认

(PLEASE RETURN A COPY WITH APPROVAL)  
(请将确认的复印件返回我司)

APPROVED

QA

MB.

J Jiang

SUZHOU HANGJING ELEC&amp;TECH CO.,LTD

苏州杭晶电子科技有限公司

No. 207, Blk. B, Chenlei Science &  
Technology Park, No. 1, First Qunxing Road,  
Suzhou Industrial Park, Jiangsu, China  
TEL 86 (0)512 65916689  
FAX 86 (0)512 65918005

Revision	Description / ECN	Prepared	Approved	Date
1	Initial release	MB	James Jiang	2023-06-13
2	Not issued			
3	Not issued			
4	Not issued			

**1. NOMINAL AND MAXIMUM RATINGS, OPERATING AND STORAGE CONDITIONS**

	PARAMETER	SYMB.	MIN	TYP	MAX	Unit	Conditions / Remarks
1	Nominal frequency	F <sub>N</sub>	<b>10.000</b>			MHz	--
2	Operating supply voltage range	V <sub>CC</sub>	4.75	5.0	5.25	V <sub>DC</sub>	
3	Output load	R <sub>L</sub>		15		pF	CMOS Level
4	Operating temperature range	T <sub>OP</sub>	-40	+25	+85	°C	Note 1
5	Storage Temperature Range	T <sub>ST</sub>	-55		+105	°C	--

Note 1: over the whole range, the unit stays within all relevant parameter limits as specified under point 2.


**2. ELECTRICAL PARAMETER LIMITS**

	PARAMETER	SYMB.	MIN	TYP	MAX	Unit	Conditions / Remarks
1	Initial Frequency Accuracy	$\Delta f/F_N$	-200		+200	ppb	Offset from nominal at +25°C
2	Frequency stability over T <sub>OP</sub>	$\Delta f/F_{OP}$	-10		+10	ppb	Over T <sub>OP</sub> Note 1
3	Short Term Stability ( in still air)				0.05	ppb/s	Max, after power on 1h
4	Warm-up Time				5.0	min	Within $\pm 20$ ppb of final frequency with reference after 1 hour on@+25°C
5	Frequency VS voltage changes	$\Delta f/F_V$	-2.0		+2.0	ppb	V <sub>CC</sub> $\pm 5\%$ at +25°C
6	Frequency VS load changes	$\Delta f/F_L$	-2.0		+2.0	ppb	CL $\pm 10\%$ at +25°C
7	Aging per day	$\Delta f/F_{Ad}$	-0.5		+0.5	ppb	Aging after 30 days of operation
8	Aging first year	$\Delta f/F_{A1}$	-100		+100	ppb	
9	Aging 10 years	$\Delta f/F_{A10}$	-0.5		+0.5	ppm	
10	Output voltage level HIGH	V <sub>OH</sub>	2.4	2.8		V <sub>DC</sub>	HCMOS level 90%V <sub>CC</sub> MIN
11	Output voltage level LOW	V <sub>OL</sub>			0.4	V <sub>DC</sub>	HCMOS level 10%V <sub>CC</sub> MAX
12	Output amplitude rise/fall time	t <sub>R</sub> t <sub>F</sub>			5.0	ns	15pF / +25°C
13	Output amplitude symmetry	DC	45		55	%	15pF / +25°C
14	Phase noise	L <sub>RMS</sub>			-90	dBc/Hz	at 1Hz offset / at +25°C
					-120		at 10Hz offset / at +25°C
					-140		at 100Hz offset / at +25°C
					-150		at 1kHz offset / at +25°C
					-155		at 10kHz offset / at +25°C
					-155		at 100kHz offset / at +25°C
15	Operating Current	I <sub>CC</sub>			750	mA	During warm up
					250		At steady state,@25°C
16	Control Voltage Range	V <sub>C</sub>	0	2.5	5	V <sub>DC</sub>	
17	Reference Voltage	V <sub>REF</sub>				V <sub>DC</sub>	NA
18	Frequency tuning range	F <sub>-PULL</sub>	$\pm 1.0$			ppm	Positive Slope

19	Linearity				10	%	
20	Input Impedance		100			KΩ	


Note 1: Referenced to midpoint between minimum and maximum frequency over specified temperature range.

### 3. PRODUCT MARKING


1	<b>10.000</b>	Nominal frequency in MHz (three digits after decimal point)											
2	<b>HCI</b>	Company logo											
3	<b>Y</b>	Year code of manufacturing (see table below)											
	<b>Year</b>	2021	2022	2023	2024	2025	2026	2027	2028	2029	2030	2031	2032
	<b>Code</b>	V	W	X	Y	Z	A	B	C	D	E	F	G
4	<b>M</b>	Month code of manufacturing (see table below)											
	<b>Month</b>	Jan	Feb	Mar	Apr	May	Jun	Jul	Aug	Sep	Oct	Nov	Dec
	<b>Code</b>	A	B	C	D	E	F	G	H	J	K	L	M

### 4. OUTLINE DRAWING

	Package description	Package model	Remarks
1	OCXO 36x27 SMD with 5 pins	3627-5P	--



### 5. TEST CIRCUIT



### 6. PACKAGING INFORMATION

Units packed into an antistatic foam tray