


客户图



- Note:
- 1: Material(材料):
 Barrel: Brass C6801 (针管: 无铅铜 C6801)
 Plunger: Brass C6801 (针头: 无铅铜 C6801)
 Spring: SUS304 (弹簧: SUS304)
 Plating(电镀):
 Barrel: 3u' Au over 50~80u' Ni(针管: 镀金3u', 镍底50~80u'.)
 Plunger: 3u' Au over 50~80u' Ni(针头: 镀金3u', 镍底50~80u'.)
 Spring: No plated(弹簧: 不电镀)
 - 2: Electrical(电气特性):
 Rated Current & Voltage: DC 12V; 2A (额定电压&电流: 直流12V, 2A)
 Contact Resistance: 50 mohm Max. at working height.
 接触电阻: 最大50毫欧(在工作高度状态下)
 - 3: Mechanical(机械性能):
 Force: 60g±20% at working height. (60g±20% 在工作高度)。
 Durability: 10,000 cycles(min) (寿命: 10000次)
 - 4: WorkTemperature(工作环境):
 Withstanding Higt Temperature: 280°C
 Operational Temperature: -20°C~ +70°C

NO.	ECN NO.	DESCRIPTION	DATE

深圳市鑫探技术有限公司 HTTP://WWW.XYZPOGOPIN.COM TEL: 0755-28773277 FAX: 0755-28891353				SCALE: N/A	UNIT: mm	THE UNMARKED TOLERANCE ARE AS BELOW: LENGTH: ±0.05mm, ±0.10mm, ±0.20mm ANGLE: ±0.50°, ±1.00°, ±2.00°		DESIGNED BY:	DWG. NO. YZ08415060P-01
SHEET: 1 of 1	PROJECTION: A.1	DATE: 2026.4.11	VER.:			CHECKED BY:		TITLE: Pogo pin连接器	