


客户图



Note:

- 1: Material(材料):
Barrel: Brass C3604 (针管: 黄铜 C3604)
Plunger: Brass C3604 (针头: 黄铜 C3604)
Spring: SUS304 (弹簧: SUS304)
- 2: Plating(电镀):
Barrel: 1u' Au over 50~80u' Ni(针管: 镀金1u', 镍底50~80u'.)
Plunger: 1u' Au over 50~80u' Ni(针头: 镀金1u', 镍底50~80u'.)
Spring: No plated (弹簧: 不电镀)
- 3: Electrical(电气特性):
Rated Current & Voltage: DC 12V,1A (额定电压&电流: 直流12V,1A)
Contact Resistance: 50 mohm Max. at working height.
接触电阻: 最大50毫欧(在工作高度状态下)
- 4: Mechanical(机械性能):
Force: 250g±20% at working height. (250g±20%在工作高度)。
Durability: 10,000 cycles(min) (寿命: 10000次)
- 5: Work Temperature(工作环境):
Withstanding Higt Temperature: 280°
Operational Temperature: -20°~ +70°

NO.	ECN NO.	DESCRIPTION	DATE

THE UNMARKED TOLERANCE ARE AS BELOW:

SCALE:	N/A	UNIT	mm
SHEET:	1 of 1	PROJECTION	
DATE:	2026.4.11	VER.	D.0

LENGTH	ANGLE
XXX ±0.05mm	X.XX ±0.50°
XX ±0.10mm	XX ±1.00°
X ±0.20mm	X ±2.00°

DESIGNED BY:	DWG. NO.
CHECKED BY:	YZ101725132P-01
APPROVED BY:	TITLE: Pogo pin连接器

深圳市鑫探技术有限公司

HTTP://WWW.XYZPOGOPIN.COM
TEL:0755-28773277 FAX:0755-28891353



1 2 3 4 5 6 7 8 9 10 11 12