

N-Channel 100V MOSFET

E100N2P3OH2

V_{DS} (V)	$R_{DS(on),max}$ (m Ω)	I_D (A)
100V	2.5 @ $V_{GS} = 10V$	210



Features

- Low $R_{DS(on)}$ trench technology
- Low thermal impedance
- Fast switching speed
- 100% avalanche tested

Applications

- DC/DC conversion
- Power switch
- PD charger
- Moto driver

TOLL-8



RoHS
COMPLIANT
HALOGEN
FREE

Package And Ordering Information

Ordering code	Package	Marking
E100N2P3OH2	TOLL-8	E100N2P3OH2

Ordering Information

Package	Units/ Reel	Reels/ Inner Box	Units/ Inner Box
TOLL-8	2000	1	2000

Key Performance Parameters

Parameter	Value	Unit
VDS, min @ Tj(max)	100	V
ID, pulse	840	A
RDS(ON), max @ VGS=10V	2.5	mΩ
Qg	75	nC

Absolute Maximum Ratings at Tj=25°C Unless Otherwise Noted

Parameter		Symbol	Limit	Unit
Drain-source voltage		V _{DS}	100	V
Gate-source voltage		V _{GS}	±20	
Continuous drain current	T _C =25°C	I _D	210	A
	T _C =100°C		-	
Pulsed drain current		I _{D,pulse}	840	
Avalanche energy, single pulse		E _{AS}	375	mJ
Power dissipation	T _C =25°C	P _D	230	W
	T _A =25°C		-	
Operating junction and storage temperature range		T _J , T _{stg}	-55 to 175	°C

Thermal Characteristics

Parameter		Symbol	Max.	Unit
Thermal resistance, junction-to-case	Steady state	R _{θJC}	0.65	°C/W
Thermal resistance, junction-to-ambient	Steady state	R _{θJA}	62	

Electrical Characteristics at Tj=25°C unless otherwise specified

Parameter	Symbol	Min.	Typ.	Max.	Unit	Test conditions
Static						
Drain to source breakdown voltage	V _{(BR)DSS}	100			V	V _{GS} = 0, I _D = 250 μA
Gate-source threshold voltage	V _{GS(th)}	2	3	4	V	V _{DS} = V _{GS} , I _D = 250 μA
Gate-body leakage	I _{GSS}			±100	nA	V _{DS} = 0 V, V _{GS} = ±20 V
Zero gate voltage drain current	I _{DSS}			1	μA	V _{DS} = 100 V, V _{GS} = 0 V
Drain-source on-resistance	R _{DS(on)}		1.9	2.5	mΩ	V _{GS} = 10 V, I _D = 50 A
Gate resistance	R _g		1.3		Ω	f=1MHz

Gate Charge						
Total gate charge	Qg		75		nC	V _{DS} = 50 V, I _D = 25 A, V _{GS} = 10 V
Gate-source charge	Qgs		22			
Gate-drain charge	Qgd		16			
Dynamic						
Turn-on delay time	t _{d(on)}		22		ns	V _{DS} = 50 V, I _D =25 A, V _{GS} = 10 V, R _{GEN} = 2 Ω
Rise time	t _r		18			
Turn-off delay time	t _{d(off)}		39			
Fall time	t _f		20			
Input capacitance	C _{iss}		5440		pF	V _{DS} =25 V, V _{GS} = 0 V, f = 100kHz
Output capacitance	C _{oss}		3800			
Reverse transfer capacitance	C _{rss}		177			
Body Diode						
Diode forward voltage	V _{SD}		-	1.3	V	V _{GS} = 0 V, I _S = 30 A
Reverse recovery time	t _{rr}		84		ns	V _R = 25 V, I _S =25 A, di/dt = 100 A/μs
Reverse recovery charge	Q _{rr}		145		nC	
Peak reverse recovery current	I _{rrm}		2.8		A	

Electrical Characteristics Diagrams




Figure 1. Typ. output characteristics




Figure 2. Typ. transfer characteristics




Figure 3. Typ. capacitances




Figure 4. Typ. gate charge




Figure 5. Drain-source breakdown voltage




Figure 6. Drain-source on-state resistance




Figure 7. Threshold voltage








Figure 8. Forward characteristic of body diode


Figure 9. Drain-source on-state resistance

Figure 10. Drain current

Figure 11. Safe operation area $T_C=25^{\circ}C$

Figure 12. Max. transient thermal impedance

Test circuits and waveforms




Figure 1. Gate charge test circuit & waveform




Figure 2. Switching time test circuit & waveforms




Figure 3. Unclamped inductive switching (UIS) test circuit & waveforms







Figure 4. Diode reverse recovery test circuit & waveforms

Package Outline Dimensions



SYMBOL	MILLIMETER		
	MIN.	NOM.	MAX.
A	2.200	2.300	2.400
A1	1.700	1.800	1.900
b	0.600	0.700	0.800
b1	9.700	9.800	9.900
b2	0.650	0.750	0.850
b3	1.100	1.200	1.300
c	0.400	0.500	0.600
D	10.300	10.400	10.500
D1	11.000	11.100	11.200
D2	3.200	3.300	3.400
D4	4.470	4.570	4.670
E	9.800	9.900	10.000
E1	8.000	8.100	8.200
E2	0.500	0.600	0.700
e	1.200 BSC		
e1	1.225 BSC		
H	11.600	11.700	11.800
H1	6.950 BSC		
H2	5.900 BSC		
i	0.100 REF.		
j	0.350 REF.		
K	3.100 REF.		
L	1.550	1.650	1.750
L1	0.600	0.700	0.800
L2	0.500	0.600	0.700
L3	0.400	0.500	0.600
Q	7.950 REF.		
R	3.000	3.100	3.200
θ	10° REF.		

Legal Disclaimer

The information given in this document shall be for illustrative purposes only and shall in no event be regarded as a guarantee of conditions or characteristics. Existar Technologies reserves the right to change any information herein. With respect to any examples, hints or any typical values stated herein and/or any information regarding the application of the product, Existar Technologies or its affiliates hereby make no representation or warranty of any kind, expressed or implied, as to any information provided hereunder, including without limitation as to the accuracy, completeness or non-infringement of intellectual property rights of any third party, and they assume no liability for the consequences of use of such information. In addition, any information given in this document is subject to customer's compliance with its obligations stated herein and any applicable legal requirements, norms and standards concerning customer's products and any use of the product of Existar Technologies in customer's applications. The information contained herein is exclusively intended for technically trained staff. No license is granted by implication under any patent right, copyright, mask work right, or other intellectual property right. It is customer's sole responsibility to evaluate the suitability of the product for the intended application and the completeness of the product information given herein with respect to such application. In no event shall Existar Technologies or its affiliates be liable to any party for any direct, indirect, special, punitive, incidental or consequential damages of any nature whatsoever, including but not limited to loss of profits and loss of goodwill, whether or not such damages are based on tort or negligence, warranty, breach of contract or any other legal theory.