


# 客户图



## Note:

- 1: Material(材料):  
 Barrel: Brass C3604 (针管: 黄铜 C3604)  
 Plunger: Brass C3604 (针头: 黄铜 C3604)  
 Spring: SUS304 (弹簧: SUS304)  
 Plating(电镀):  
 Barrel: 3u' Au over 50~80u' Ni(针管: 镀金3u', 镍底50~80u'.)  
 Plunger: 3u' Au over 50~80u' Ni(针头: 镀金3u', 镍底50~80u'.)  
 Spring: No plated (弹簧: 不电镀)
- 3: Electrical(电气特性):  
 Rated Current & Voltage: DC 12V; 1A (额定电压&电流: 直流12V, 1A)  
 Contact Resistance: 50 mohm Max. at working height.  
 接触电阻: 最大50毫欧 (在工作高度状态下)
- 4: Mechanical(机械性能):  
 Force: 20g±5g at working height. (20g±5g 在工作高度)。  
 Durability: 10,000 cycles(min) (寿命: 10000次)  
 5: Work Temperature(工作环境):  
 Withstanding Higt Temperature: 280°  
 Operational Temperature: -40°~ +85°

NO.	ECN NO.	DESCRIPTION	DATE
1			

## 深圳市鑫探技术有限公司

HTTP://WWW.XYZPOGOPIN.COM  
 TEL:0755-28773277 FAX:0755-28891353



SCALE:	N/A	UNIT	mm
SHEET:	1 of 1	PROJECTION	⊕
DATE:	2026.4.11	VER.	A.0

THE UNMARKED TOLERANCE ARE AS BELOW:

LENGTH	ANGLE
XXX ±0.05mm	X.XX ±0.50°
XX ±0.10mm	XX ±1.00°
X ±0.20mm	X ±2.00°

DESIGNED BY:	DWG. NO.	YZ107715095P-01
CHECKED BY:	TITLE:	Pogo pin
APPROVED BY:		