



修 订	标 记	修 改 描 要	签 名	日 期
REV A0		NEW DWG		2016-03-12



sPECIFICATION

1.Electrical characteristics

Contact Current Rating:0.5 A

Dielectric Withstanding Voltange:300V AC

Insulation Resistance:a.Mate 100MΩ MIN at 500V/DC
b.Unmate 10MΩ MIN at 150V/DC

Contact Resistance:30mΩ MAX

Temperature Range:-20° C to +85° C

2.Mechanical

Mating Face:44.1N MAX

Unmatin Face:9.8N MIN;39.2N MAX

Durability:5000 Cycles

3.material:

PVC:45Pa, UL94V-0;

HOUSING:THERMOPLASTICS HIGH TEMP LCP+GLASS
FIBER BLACK COLOR, UL94V-0





CONTACT:BRASS , T=0.20MM

SHELL:C2680 , T=0.40MM

4. PLATING:

CONTACT:1u" GOLD/TIN PLATING ON CONTACT AREA
50u"MIN, NICKEL UNDERPLATING OVER ALL

Shell: G/F plated over 50u" NI min.



		深 圳 市 华 德 共 创 科 技 有 限 公 司 Shenzhen Huade co-create Technology Co., LTD 电 话 : 0755-27111216 传 真 : 0755-29940187					
-TOLERANCES- UNLESS OTHERWISE SPECIFIED 公差参数表				TITLE: HDMI AF转接头铁壳镀镍黑胶 产品名称: 成型L=28.8			
X.X	±0.30	X.X*	±3°	APPD: 核准:	PART NO: 产品编号: HDMI-GD-139PWB		
X.XX	±0.20	X.XX*	±2°	CHECK: 校对: 王建业	DATE	SCALE	UNIT
X.XXX	±0.10	X.XXX*	±1°	DRAW: 绘图: 黄艳兰	2016-03-12	1:1	mm
							A001