

修 订	标 记	修 改 描 要	签 名	日 期
REV	AO	NEW DWG		2016-03-12

NOTES:

- 1.HUOSING: LCP HIGH-TEMP THERMOPLASTIC UL94V-0 COLOR:BLACK
- 2.ACTUATOR: LCP HIGH-TEMP THERMOPLASTIC UL94V-0 COLOR:BLACK
- 3.TERMINAL:PHOSPHOR BRONZE
PLATING:1* "GOLD FLASH OR 100~150* "TIN(LEAD FREE)
OVERALL 50~100* "NICKEL UNDER PLATED.
- 4.FITTING NAIL:BRASS
PLATING:100~150* "TIN(LEAD FREE)
- 5.RATING: OVERALL 50~100* "NICKEL UNDER PLATED.

OPERATING VOLTAGE:50V AC,DC
CURRENT RATING:0.5A AC,DC
OPERATING TEMPERATURE:-40°C~+85°C

NO.of contacts	Dimensions				NO.of contacts	Dimensions			
	A.	B.	C.	D.		A.	B.	C.	D.
8	8.92	3.50	4.63	6.87	36	22.92	17.50	18.63	20.87
9	9.42	4.00	5.13	7.37	38	23.92	18.50	19.63	21.87
10	9.92	4.50	5.63	7.87	40	24.92	19.50	20.63	22.87
11	10.42	5.00	6.13	8.37	41	25.42	20.00	21.13	23.37
12	10.92	5.50	6.63	8.87	42	25.92	20.50	21.63	23.87
13	11.42	6.00	7.13	9.37	45	27.42	22.00	23.13	25.37
14	11.92	6.50	7.63	9.87	46	27.92	22.50	23.63	25.87
15	12.42	7.00	8.13	10.37	48	28.92	23.50	24.63	26.87
16	12.92	7.50	8.63	10.87	49	29.42	24.00	25.13	27.37
17	13.42	8.00	9.13	11.37	50	29.92	24.50	25.63	27.87
18	13.92	8.50	9.63	11.87	51	30.42	25.00	26.13	28.37
19	14.42	9.00	10.13	12.37	52	30.92	25.50	26.63	28.87
20	14.92	9.50	10.63	12.87	53	31.42	26.00	27.13	29.37
21	15.42	10.00	11.13	13.37	54	31.92	26.50	27.63	29.87
22	15.92	10.50	11.63	13.87	55	32.42	27.00	28.13	30.37
23	16.42	11.00	12.13	14.37	56	32.92	27.50	28.63	30.87
24	16.92	11.50	12.63	14.87	57	33.42	28.00	29.13	31.37
25	17.42	12.00	13.13	15.37	58	33.92	28.50	29.63	31.87
26	17.92	12.50	13.63	15.87	59	34.42	29.00	30.13	32.37
27	18.42	13.00	14.13	16.37	60	34.92	29.50	30.63	32.87
28	18.92	13.50	14.63	16.87	61	35.42	30.00	31.13	33.37
29	19.42	14.00	15.13	17.37	62	35.92	30.50	31.63	33.87
30	19.92	14.50	15.63	17.87	63	36.42	31.00	32.13	34.37
31	20.42	15.00	16.13	18.37	64	36.92	31.50	32.63	34.87
32	20.92	15.50	16.63	18.87	65	37.42	32.00	33.13	35.37
33	21.42	16.00	17.13	19.37	66	37.92	32.50	33.63	35.87
34	21.92	16.50	17.63	19.87	68	38.92	33.50	34.63	36.87
35	22.42	17.00	18.13	20.37	80	44.92	39.50	40.63	42.87



深圳市华德共创科技有限公司
Shenzhen Huade co-create Technology Co.,LTD
电话：0755-27111216 传真：0755-29940187



-TOLERANCES-
UNLESS OTHERWISE SPECIFIED
公差参数表

X.X	±0.30	X.X*	±3°
X.XX	±0.20	X.XX*	±2°
X.XXX	±0.10	X.XXX*	±1°






APPD:
核准:
CHECK:
校对: 王建业
DRAW:
绘图: 黄艳兰

TITLE: 产品名称: FPC0.5间距2.5高掀盖下接带扣			
PART NO: 产品编号:	HDGC0525-xxCL-GF		
DATE	SCALE	UNIT	CODE NUMBER
2016-03-12	1:1	mm	A001





RECOMMENDED PCB PATTERN DIM.

TOLERANCE : ±0.05



CABLE INSERT DIM.




APPLICABLE FPC/FFC

APPLICABLE FPC/FFC


修 订	标 记	修 改 描 要	签 名	日 期
REV AO		NEW DWG		2016-03-12

REEL Dim







No. of	DIM.			REEL (CARTON)	
Contacts	A	B	C	REEL (CARTON)	SUM (PCS)
8pin~9pin	16	7.5	—	15	30000
10pin~24pin	24	11.5	—	10	20000
25pin~35pin	32	14.2	28.4	8	16000
36pin~40pin	44	20.2	40.4	6	12000
41pin~50pin	44	20.2	40.4	6	9000
51pin~60pin	56	26.25	52.5	5	7500
80pin	72	34.25	68.4	4	6000

Tape width 16 and 24 mm



Tape width 32 and 56 mm



MEAS:35*35*35 CM

- Notes:
- 1.Component load per 13" reel:2000 (for4P~40P)
Component load per 13" reel:1500 (for41P~80P)
 - 2.Material : Black Conductive Polystyrene Alloy.
 - 3.Thickness : 0.3±0.05mm
 - 4.All dimensions meet EIA-481-C requirements.



深圳市华德共创科技有限公司
Shenzhen Huade co-create Technology Co.,LTD
电话：0755-27111216 传真：0755-29940187

-TOLERANCES- UNLESS OTHERWISE SPECIFIED 公差参数表		TITLE: 产品名称: FPC0.5间距2.5高掀盖下接带扣	
X.X ±0.30	X.X* ±3°	APPD: 核准:	PART NO: 产品编号: HDGC0525-xxCL-GF
X.XX ±0.20	X.XX* ±2°	CHECK: 校对: 王建业	DATE SCALE UNIT CODE NUMBER
X.XXX ±0.10	X.XXX* ±1°	DRAW: 绘图: 黄艳兰	2016-03-12 1:1 mm A001