

产品规格书

Product Specification

CUSTOMER 客户: _____

CUSTOMER PN 客户 PN: _____

HANG CRYSTAL P/N 杭晶物料编码: 5214H4-25.000A33DTNOL

MODEL 产品型号: OCXO DIP-14, HCMOS, 3.3V

NOMINAL FREQUENCY 频率: 25.000MHz

ISSUE DATE 日期: 2025 / 05 / 19

CUSTOMER'S APPROVAL

客户确认

(PLEASE RETURN A COPY WITH APPROVAL)
(请将确认的复印件返回我司)

APPROVED

QA

MB.

J Jiang

SUZHOU HANGJING ELEC&TECH CO., LTD

苏州杭晶电子科技有限公司

No. 207, Blk. B, Chenlei Science & Technology Park, No. 1, First Qunxing Road, Suzhou Industrial Park, Jiangsu, China
TEL 86 (0)512 65916689
FAX 86 (0)512 65918005

Revision	Description / ECN	Prepared	Approved	Date
1	Initial release	MB	James Jiang	2025-05-19
2	Not issued			
3	Not issued			
4	Not issued			

1. NOMINAL AND MAXIMUM RATINGS, OPERATING AND STORAGE CONDITIONS

	PARAMETER	SYMB.	MIN	TYP	MAX	Unit	Conditions / Remarks
1	Nominal frequency	F_N	25.000			MHz	--
2	Operating supply voltage range	V_{CC}	3.135	3.3	3.465	V_{DC}	
3	Output load	R_L		15		pF	CMOS Level
4	Operating temperature range	T_{OP}	-40	+25	+85	°C	Note 1
5	Storage Temperature Range	T_{ST}	-55		90	°C	--

Note 1: over the whole range, the unit stays within all relevant parameter limits as specified under point 2.

2. ELECTRICAL PARAMETER LIMITS

	PARAMETER	SYMB.	MIN	TYP	MAX	Unit	Conditions / Remarks
1	Initial Frequency Accuracy	$\Delta f/F_N$	-100		+100	ppb	Offset from nominal at +25°C
2	Frequency stability over T_{OP}	$\Delta f/F_{OP}$	-100		+100	ppb	Over T_{OP} Note 1
3	Short Term Stability (in still air)				0.05	ppb/s	Max, after power on 1h
4	Warm-up Time				3.0	min	Within ± 100 ppb of final frequency with reference after 1 hour on@+25°C
5	Frequency VS voltage changes	$\Delta f/F_V$	-5.0		+5.0	ppb	$V_{CC} \pm 5\%$ at +25°C
6	Frequency VS load changes	$\Delta f/F_L$	-5.0		+5.0	ppb	$CL \pm 10\%$ at +25°C
7	Aging per day	$\Delta f/F_{Ad}$	-3.0		+3.0	ppb	Aging after 30 days of operation
8	Aging first year	$\Delta f/F_{A1}$	-500		+500	ppb	
9	Aging 10 years	$\Delta f/F_{A1}$	-1.5		+1.5	ppm	
10	Frequency stability overall	$\Delta f/F_N$	-4.6		+4.6		Within 20 years
11	Output voltage level HIGH	V_{OH}	2.4	2.8		V_{DC}	
12	Output voltage level LOW	V_{OL}			0.4	V_{DC}	
13	Output amplitude rise/fall time	$t_{r} t_{f}$			5.0	ns	15pF / +25°C
14	Output amplitude symmetry	DC	45		55	%	15pF / +25°C
15	Phase noise	L_{RMS}			-110	dBc/Hz	at 10Hz offset / at +25°C
					-130		at 100Hz offset / at +25°C
					-145		at 1kHz offset / at +25°C
					-150		at 10kHz offset / at +25°C
					-150		at 100kHz offset / at +25°C
16	Operating Current	I_{CC}			750	mA	During warm up
					250	mA	At steady state,@25°C
17	Control Voltage Range	V_C				V_{DC}	NA
18	Frequency tuning range	F_{PULL}				ppm	NA
19	Linearity					%	NA


Note 1: Frequency stability is the frequency deviation over operating temperature range T_{OP} in reference to the frequency reading at +25°C.

3. PRODUCT MARKING


1	FF.fff	Nominal frequency in MHz (three digits after decimal point)										HCI YM FF.fffMHz ● H33ADTNO				
2	HCI	Company logo														
3	Y	Year code of manufacturing (see table below)														
	Year	2021	2022	2023	2024	2025	2026	2027	2028	2029	2030	2031	2032			
	Code	V	W	X	Y	Z	A	B	C	D	E	F	G			
4	M	Month code of manufacturing (see table below)														
	Month	Jan	Feb	Mar	Apr	May	Jun	Jul	Aug	Sep	Oct	Nov	Dec			
	Code	A	B	C	D	E	F	G	H	J	K	L	M			

4. OUTLINE DRAWING

	Package description	Package model	Remarks
1	20x13 DIP type with 4 pins	DIP-14h11	Pin 1 N.C.



5. TEST CIRCUIT



6. ENVIRONMENTAL COMPLIANCE INFORMATION

▪ RoHS COMPLIANCE

We can certify herewith that the product is fully RoHS complaint according the “DIRECTIVE 2011/65/EU OF THE EUROPEAN COUNCIL OF 27. JANUARY 2003 ON THE RESTRICTION OF THE USE OF CERTAIN HAZARDOUS SUBSTANCES” in electrical and electronic equipment (RoHS) and its amendments.

The product contains Lead (Pb) in high melting point solder alloy with >85% Lead and falls under RoHS exemption 7a.

In regards of RoHS 2, CE marking directive for finished products, we can provide RoHS test reports and MDS to show compliance, but since our product is not a final application we have no CE mark

▪ HALOGEN FREE

We can certify that this product is Halogen-Free per IEC 61249-2-21:2003.

▪ ELECTROSTATIC DISCHARGE (ESD) SENSITIVITY

This product is sensitive to ELECTROSTATIC DISCHARGE (ESD), precautions for handling and storage shall be applied based on suggested internal standards listed below.

(JEITA EIAJ ED-4701 / JSD22 / ANSI-ESD-S20-20 / IEC 61000-4-2)

▪ MOISTURE SENSITIVITY (MSL) CLASSIFICATION [J-STD-020C]

This product in a hermetically sealed package does NOT fall under the classification of moisture sensitivity per above stated standard (standard is for non-hermetically sealed components).

If customer's system requires an entry in this regard we suggest using LEVEL 1.

7. PACKAGING INFORMATION

PACKAGING IN ESD CONFORM PLASTIC TUBES OR TRAY STAPLED INTO A CARDBOARD BOX.