








Mated Condition

NOTES:

- 1. MATERIAL AND PLATING:**
Housing: LCP+30%G.F,UL 94V-0,Black
CAP: LCP+30%G.F,UL 94V-0,Black
Contact: Copper Alloy, Au And Sn Plated.
Shell: C2680-H, Ni Plated.
- 2. MECHANICAL CHARACTERISTIC**
Mating Force: 44.1N(4.5Kgf) max.
Unmating Force: 9.8N~39.2(1~4Kgf).
Durability: 10,000 Cycles.
- 3. ELECTRICAL CHARACTERISTIC**
Contact Resistance: 30m Ohm Max.
Insulation Resistance: 100M Ohm Min(unmated)
10M Ohm Min(mated)
Dielectric Withstanding Voltage: 500V AC Min
- 4. TEMPERATURE**
Operating Temperature: -40?~+85?
Storage Temperature: -60?~+105?



深圳市华德共创科技有限公司
Shenzhen Huade co-create Technology Co.,LTD
电话: 0755-27111216 传真: 0755-29940187

-TOLERANCES- UNLESS OTHERWISE SPECIFIED 公差参数表		TITLE: 产品名称: HDMI AF RA TYPE侧面双螺丝孔	
X.X ±0.30	X.X* ±3°	APPD: 核准:	PART NO: 产品编号: HDMI-GD-106PWB
X.XX ±0.20	X.XX* ±2°	CHECK: 校对: 王建业	DATE SCALE UNIT CODE NUMBER
X.XXX ±0.10	X.XXX* ±1°	DRAW: 绘图: 黄艳兰	2016-03-12 1:1 mm A001