

Features

150 Watts peak pulse power ($t_p = 8/20\mu s$)
 Tiny SOT143 package
 Bidirectional configurations
 Solid-state silicon-avalanche technology
 Low clamping voltage
 Low leakage current
 Low capacitance ($C_j=30pF$ typ I/O to I/O.)
 Protection one data/power line to:
 IEC 61000-4-2 $\pm 8kV$ contact $\pm 15kV$ air
 IEC 61000-4-4 (EFT) 40A (5/50ns)
 IEC 61000-4-5 (Lightning) 10A (8/20 μs)

Mechanical Data

SOT143 package
 Molding compound flammability rating: UL 94V-0
 Packaging: Tape and Reel
 RoHS/WEEE Compliant


Applications

USB2.0,
 Ethernet
 Notebooks, Desktops, and Servers
 Video Line Protection

503B



SOT143



Schematic & PIN Configuration

Absolute Maximum Rating


Rating	Symbol	Value	Units
Peak Pulse Power ($t_p = 8/20\mu s$)	P_{PP}	150	Watts
Peak Pulse Current ($t_p = 8/20\mu s$) (note1)	I_{pp}	10	A
ESD per IEC 61000-4-2 (Air) ESD per IEC 61000-4-2 (Contact)	V_{ESD}	15 8	kV
Lead Soldering Temperature	T_L	260(10seconds)	$^{\circ}C$
Junction Temperature	T_J	-55 to + 125	$^{\circ}C$
Storage Temperature	T_{stg}	-55 to + 125	$^{\circ}C$

Electrical Characteristics (TA = 25°C unless otherwise noted)

Part Number	Device Marking	V _{RWM} (V)	V _{BR} (V)	I _T (mA)	V _C @1A	V _C		I _R μA (Max)	C (Pf) (Typ.)
						(Max)	(@A)		
SP0503BAHTG	503B	5	6	1	10	15	10	1	30

Electronics Parameter (TA = 25°C unless otherwise noted)

Symbol	Parameter
I _{PP}	Maximum Reverse Peak Pulse Current
V _C	Clamping Voltage @ I _{PP}
V _{RWM}	Working Peak Reverse Voltage
I _R	Maximum Reverse Leakage Current @ V _{RWM}
V _{BR}	Breakdown Voltage @ I _T
I _T	Test Current



Note: 8/20μs pulse waveform.

RATING AND CHARACTERISTIC CURVES

Figure 1: Peak Pulse Power vs. Pulse Time




Figure 2: Power Derating Curve




Figure3: Pulse Waveform





Figure 4: Clamping Voltage vs. I_pp




Soldering parameters


Reflow Condition		Pb-Free assembly (see as below)
Pre Heat	-Temperature Min ($T_{s(min)}$)	+150°C
	-Temperature Max($T_{s(max)}$)	+200°C
	-Time (Min to Max) (ts)	60-180 secs.
Average ramp up rate (Liquid us Temp (T_L) to peak)		3°C/sec. Max
$T_{s(max)}$ to T_L - Ramp-up Rate		3°C/sec. Max
Reflow	-Temperature(T_L)(Liquid us)	+217°C
	-Temperature(t_L)	60-150 secs.
Peak Temp (T_P)		+260(+0/-5)°C
Time within 5°C of actual Peak Temp (t_p)		30 secs. Max
Ramp-down Rate		6°C/sec. Max
Time 25°C to Peak Temp (T_P)		8 min. Max
Do not exceed		+260°C



Package Dimensions & Suggested Pad Layout



SOT-143





SYMBOL	DIMENSIONS			
	MILLIMETER		INCHES	
	MIN	MAX	MIN	MAX
A	0.900	1.150	0.035	0.045
A1	0.000	0.100	0.000	0.004
A2	0.900	1.050	0.035	0.041
b	0.300	0.500	0.012	0.020
b1	0.750	0.900	0.030	0.035
D	2.800	3.000	0.110	0.118
e	1.800	2.000	0.071	0.079
e1	0.200TYP		0.008TYP	
E	2.250	2.550	0.089	0.100
E1	1.200	1.400	0.047	0.055
θ	0°	8°	0°	8°
aaa	.006		0.15	
bbb	.008		0.20	
ccc	.004		0.10	

Dimensions	Value (in mm)
Z	2.90
G	1.20
X	2.50
X1	1.00
X2	0.60
Y	0.85
C	2.05

Dimensions in inches and (millimeters)

Tape & reel specification

Tape	Symbol	Dimension (mm)
	P0	4.00±0.20
	P1	4.00±0.20
	P2	2.00±0.20
	D0	1.55±0.20
	D1	1.20±0.20
	E	1.55±0.25
	F	3.60±0.20
	W	8.00±0.20
	A0	3.80±0.20
	B0	3.10±0.20
	K0	1.40±0.20
	T	0.20±0.20
	7" Reel	D2
	D3	55Min.
	D4	R24.6±2.0
	G	R82.0±2.0
	I	13.0±2.0
	W1	10.20±3.0
	Quantity: 3000PCS	