

### Features

150W peak pulse power(8/20 $\mu$ s)  
Ultra low leakage: nA level  
Operating voltage: 7V or 12V  
Low clamping voltage  
Complies with following standards:  
– IEC 61000-4-2 (ESD) immunity test  
    Air discharge:  $\pm 30$ kV  
    Contact discharge:  $\pm 30$ kV  
– IEC61000-4-4 (EFT) 40A (5/50ns)  
– IEC61000-4-5 (Lightning) 7A (8/20 $\mu$ s)  
RoHS Compliant

### Mechanical Data


Package: SOT-23  
Lead Finish: Matte Tin  
Case Material: "Green" Molding Compound.  
UL Flammability Classification Rating 94V-0  
Moisture Sensitivity: Level 3 per J-STD-020  
Terminal Connections: See Diagram Below

### Applications


Wireless System  
Networks  
Portable Instrumentation  
RS485 Ports



#### SOT-23



1.BASE  
2.EMITTER  
3.COLLECTOR



**Schematic & PIN Configuration**

### Absolute Maximum Rating


Parameter	Symbol	Value	Unit
Peak Pulse Power(8/20 $\mu$ s)	Ppk	150	W
Peak Pulse Current(8/20 $\mu$ s)	IPP	7	A
ESD per IEC 61000-4-2 (Air)	VESD	$\pm 30$	kV
ESD per IEC 61000-4-2 (Contact)		$\pm 30$	
Operating Temperature Range	TJ	-55 to +125	$^{\circ}$ C
Storage Temperature Range	Tstg	-55 to +150	$^{\circ}$ C

## Electrical Characteristics (TA=25°C unless otherwise specified)


Parameter	Symbol	Pin 1 to 3 and 2 to 3(12V TVS)			Pin 3to 1 and 3 to 2(7V TVS)			Unit	Test Condition
		Min	Typ	Max	Min	Typ	Max		
Reverse Working Voltage	VRWM			12			7	V	
Breakdown Voltage	VBR	13.3			7.5			V	IT = 1mA
Reverse Leakage Current	IR		0.01	0.5		0.01	0.5	μA	VR = VRWM
Clamping Voltage	VC			19			11	V	IPP = 1A (8 x 20μs pulse)
Clamping Voltage	VC			25			15	V	IPP = 7A (8 x 20μs pulse)
J unction Capacitance	CJ			75			75	pF	VR=0, f=1MHz
J unction Capacitance	CJ		45			45		pF	VR=VRWM, f=1MHz

**RATING AND CHARACTERISTIC CURVES**


**Fig1. 8/20μs Pulse Waveform**



**Fig2. ESD Pulse Waveform (according to IEC 61000-4-2)**



**Fig3. Power Derating Curve**





Soldering parameters

Reflow Condition		Pb-Free assembly (see as below)
Pre Heat	-Temperature Min ( $T_{s(min)}$ )	+150°C
	-Temperature Max( $T_{s(max)}$ )	+200°C
	-Time (Min to Max) (ts)	60-180 secs.
Average ramp up rate (Liquid us Temp ( $T_L$ ) to peak)		3°C/sec. Max
$T_{s(max)}$ to $T_L$ - Ramp-up Rate		3°C/sec. Max
Reflow	-Temperature( $T_L$ )(Liquid us)	+217°C
	-Temperature( $t_L$ )	60-150 secs.
Peak Temp ( $T_P$ )		+260(+0/-5)°C
Time within 5°C of actual Peak Temp ( $t_p$ )		30 secs. Max
Ramp-down Rate		6°C/sec. Max
Time 25°C to Peak Temp ( $T_P$ )		8 min. Max
Do not exceed		+260°C



Package Dimensions & Suggested Pad Layout

SOT23



SOT-23 mechanical data

UNIT	A	C	D	E	He	e	M	L	L <sub>1</sub>	a	
mm	max	1.1	0.15	1.4	3.0	2.6	0.5	1.95	0.55 (ref)	0.36 (ref)	0.0
	min	0.9	0.08	1.2	2.8	2.2	0.3	1.7			0.15
mil	max	43	6	55	118	102	20	77	22 (ref)	14 (ref)	0.0
	min	35	3	47	110	87	12	67			6

Dimensions	SOT23
Z	2.9
X	0.8
Y	0.9
C	2.0
E	1.35

Tape & reel specification

Tape		Symbol	Dimension (mm)		
		P0	4.00±0.10		
		P1	4.00±0.10		
		P2	2.00±0.10		
		D0	1.55±0.10		
		D1	1.05±0.10		
		E	1.55±0.10		
		F	3.60±0.10		
		W	8.00±0.10		
		A0	3.80±0.20		
		B0	3.25±0.20		
		K0	1.45±0.10		
		T	0.25±0.05		
		7" Reel		D2	178.0±3.0
				D3	55Min.
				D4	R24.0±3.0
G	R82.0±3.0				
I	13.0±2.0				
W1	11.0±3.0				
		Quantity: 3000PCS			