





ROHS

REV.	ECN NO.	DESCRIPTION	DRAW	DATE

SPECIFICATION:
Voltage Rating: 250V
Current Rating: 2AMP
Temperature Range: -40℃to+105℃
Contact Resistance: 20mΩ Max
Insulation Resistance: 1000MΩ Min
Withstanding Voltag : AC 500V
Material:
Insulator: Polyester (UL94V-0)
Standard: PA6T
Contact: Brass
Plating: Au over Ni



PCB LAYOUT General±0.05mm.

CUSTOMER DRAWING		LAILAN 深圳市莱联电子有限公司			
DRAWING		SHENZHEN LAILIAN ELECTRONICS CO., LTD			
CHECKED					
APPROVED		TITLE		排针 PIN距2.0 壁厚2.0 双排10PIN直插	REV. A
TOLERANCES ARE		PART NO.		LAIL-PZ2.0-10PX2-L	UNITS mm
30-150	±0.35	DWG. NO.		Projection	
10-30	±0.2				
5-10	±0.15				
0-5	±0.1				
ANGLE		±3°			