



Part No	Pin	A	B	C
XY-SM2B-SRSS-TB	2	1.00	4.35	2.60
XY-SM3B-SRSS-TB	3	2.00	5.35	3.60
XY-SM4B-SRSS-TB	4	3.00	6.35	4.60
XY-SM5B-SRSS-TB	5	4.00	7.35	5.60
XY-SM6B-SRSS-TB	6	5.00	8.35	6.60
XY-SM7B-SRSS-TB	7	6.00	9.35	7.60
XY-SM8B-SRSS-TB	8	7.00	10.35	8.60
XY-SM9B-SRSS-TB	9	8.00	11.35	9.60
XY-SM10B-SRSS-TB	10	9.00	12.35	10.60
XY-SM11B-SRSS-TB	11	10.00	13.35	11.60
XY-SM12B-SRSS-TB	12	11.00	14.35	12.60
XY-SM13B-SRSS-TB	13	12.00	15.35	13.60
XY-SM14B-SRSS-TB	14	13.00	16.35	14.60
XY-SM15B-SRSS-TB	15	14.00	17.35	15.60
XY-SM16B-SRSS-TB	16	15.00	18.35	16.60
XY-SM20B-SRSS-TB	20	19.00	22.35	20.60

NOTES:

- 1.BASE: LCP
- 2.PIN: Brass
- 3.Solder Tab: Brass

SPECIFICATIONS:

- 1.Spacing: 1.0
- 2.Voltage Rating: 50V AC DC
- 3.Current Rating: 1A AC DC
- 4.Insulation Resistance: 100MΩ Min
- 5.Contact Resistance: 30mΩ Max
- 6.Withstanding voltage: 250V AC 1/Minute
- 7.Temperatuer Range: -40° ~+ 85°

DIMENSION IN mm		厦门市辛译精密电子有限公司 Xiamen XinYi Xyconn Electronics Co.,Ltd		
TOLERANCE UNLESS OTHERWISE SPECIFIED		APR. Alex	TITLE: WAFER 1.00 焊片	
.X±0.2	X.*± 5°	CHK. Jack	DWG NO. XY-SMNB-SRSS-TB	
.XX±0.1	.X.*± 3°	DRA. Can	PROJ.	CUSTOMER DRAWING
.XXX±0.05	.XX.*± 1°	SIZE A4	SCALE 1:1	SHEET 1/1 REV. A