



REV.	Q'TY	ECN. NO.	APR.	DATE	
Part No		Pin	A	B	C
XY-S2B-ZR-SM4A-TF		2	1.50	6.00	3.65
XY-S3B-ZR-SM4A-TF		3	3.00	7.50	5.15
XY-S4B-ZR-SM4A-TF		4	4.50	9.00	6.65
XY-S5B-ZR-SM4A-TF		5	6.00	10.50	8.15
XY-S6B-ZR-SM4A-TF		6	7.50	12.00	9.65
XY-S7B-ZR-SM4A-TF		7	9.00	13.50	11.15
XY-S8B-ZR-SM4A-TF		8	10.50	15.00	12.65
XY-S9B-ZR-SM4A-TF		9	12.00	16.50	14.15
XY-S10B-ZR-SM4A-TF		10	13.50	18.00	15.65
XY-S11B-ZR-SM4A-TF		11	15.00	19.50	17.15
XY-S12B-ZR-SM4A-TF		12	16.50	21.00	18.65
XY-S13B-ZR-SM4A-TF		13	18.00	22.50	20.15
XY-S14B-ZR-SM4A-TF		14	19.50	24.00	21.65
XY-S15B-ZR-SM4A-TF		15	21.00	25.50	23.15
XY-S16B-ZR-SM4A-TF		16	22.50	27.00	24.65

NOTES:

- 1.BASE: LCP
- 2.PIN: Brass
- 3.Solder Tab: Brass

SPECIFICATIONS:

- 1.Spacing: 1.5
- 2.Voltage Rating: 250V AC DC
- 3.Current Rating: 1A AC DC
- 4.Insulation Resistance: 500MQ Min
- 5.Contact Resistance: 20mΩ Max
- 6.Withstanding voltage: 500V AC 1/Minute
- 7.Temperatuer Range: -25℃ ~+ 85℃

DIMENSION IN mm		厦门市辛译精密电子有限公司 Xiamen XinYi Xyconn Electronics Co.,Ltd			
TOLERANCE UNLESS OTHERWISE SPECIFIED		APR.	Alex	TITLE: WAFER 1.50 规格	
.X±0.2	X.*± 5'	CHK.	Jack	DWG NO. XY-SNB-ZR-SM4A-TF	
.XX±0.1	.X.*± 3'	DRA.	Can	PROJ.  CUSTOMER DRAWING	
.XXX±0.05	.XX.*± 1'	SIZE	A4	SCALE	1:1
		SHEET	1/1	REV.	A