

GBJ50005 THRU GBJ5010

General Bridge Rectifiers



Voltage: 50~1000 Volts	Current: 50 Amperes	Package: GBJ
-------------------------------	----------------------------	---------------------

Features

- NH'S Standard Rectifier Chip Technology
- Low Forward Voltage Drop For High Efficiency
- Low Leakage Current For High Reliability
- High Surge Capability For High Reliability


Mechanical Data

- **Case:** Molded With UL-94 ClassV-0 Recognized, RoHS-Compliant
- **Polarity:** Look At The Diagram And Polarity On The Right
- **Terminals:** Tin Plated Leads,Solderable Per J-STD-002 And JESD22-B102


Typical Applications

- Switch Mode Power Supplies (SMPS)
- Fast Chargers
- LED Driver And Monitor Lighting
- Automotive Electronics And Charging Posts

Diagram:



Polarity:



Single Phase,Half Wave,60Hz,Resistive Or Inductive Load.For Capacitive Load,Derate Current By 20%

Maximum Ratings (Ta=25°C Unless Otherwise Specified)

Parameter	Test Conditions	Symbol	GBJ 50005	GBJ 5001	GBJ 5002	GBJ 5004	GBJ 5006	GBJ 5008	GBJ 5010	Unit
Maximum Repetitive Peak Reverse Voltage		V_{RRM}	50	100	200	400	600	800	1000	V
Maximum RMS Voltag		V_{RMS}	35	70	140	280	420	560	700	V
Maximum DC Blocking Voltage		V_{DC}	50	100	200	400	600	800	1000	V
Maximum Average Forward Rectified Current	With Heatsink 100 °C Without 25 °C	$I_{F(AV)}$	50 5.2							A
Peak Forward Surge Current Per Diode	8.3ms Single Half Sine-wave Superimposed On Rate Load	I_{FSM}	500							A
Current Squared Time Per Diode	$t < 8.3ms$	I^2t	1037.5							A ² sec
Maximum Mounting Torque	M3 srew	T_{MM}	1.1							N.m

Electrical Characteristics (Ta=25°C Unless Otherwise Specified)

Parameter	Test Conditions	Symbol	GBJ 50005	GBJ 5001	GBJ 5002	GBJ 5004	GBJ 5006	GBJ 5008	GBJ 5010	Unit
Instaneous Forward Voltage Per Diode	$I_F = 25.0 A$	V_F	1.0							V
Maximum DC Reverse Current at Rated DC Blocking Voltage	Ta=25°C , $V_R = V_{RRM}$ Ta=125°C , $V_R = V_{RRM} * 80%$	I_{RRM}	5 200							uA
Typical Junction Capacitance Per Diode	4 V,1MHz	C_J	160							pF

Thermal Characteristics (Ta=25°C Unless Otherwise Specified)

Parameter	Test Conditions	Symbol	GBJ 50005	GBJ 5001	GBJ 5002	GBJ 5004	GBJ 5006	GBJ 5008	GBJ 5010	Unit
Operating Junction Temperature Range		T_J	-55~150							°C
Storage Temperature Range		T_{STD}	-55~150							
Thermal Resistance Junction To Ambient With Steady-State	Still Air Environment With Ta=25°C	$R_{\theta JA}$	12.0							°C/W
Thermal Resistance Junction-Case With Steady-State	Device Mounted On 75mm x 45mm x 2.5mm Alu. Heat.	$R_{\theta JC}$	0.9							

Notes: 1.Pulse Test: 300 Us Pulse Width,1% Duty Cycle

GBJ50005 THRU GBJ5010

General Bridge Rectifiers



Typical Characteristics Curves




Fig.1-FORWARD CURRENT DERATING CURVE




Fig.2- TYPICAL INSTANTANEOUS FORWARD




Fig.3- TYPICAL REVERSE CHARACTERISTICS




Fig.4- TYPICAL JUNCTION CAPACITANCE





Fig.5-MAX. NON-REPETITIVE SURGE CURRENT

GBJ50005 THRU GBJ5010
General Bridge Rectifiers




OUTLINE DRAWINGS



GBJ

OUTLINE DIMENSIONS						
Dim.	Milimeters			Inches		
	Min.	Typ.	Max.	Min.	Typ.	Max.
A	29.00	-	31.00	1.1417	-	1.2205
B	19.00	-	21.00	0.7480	-	0.8268
C	3.45	-	3.95	0.1358	-	0.1555
D	4.35	-	4.85	0.1713	-	0.1909
E	0.50	-	0.90	0.0197	-	0.0354
F	5.20	-	5.80	0.2047	-	0.2283
G	3.75	-	4.25	0.1476	-	0.1673
H	2.00	-	2.40	0.0787	-	0.0945
J	0.80	-	1.20	0.0315	-	0.0472
L	13.00	-	15.00	0.5118	-	0.5906
M	9.50	-	10.50	0.3740	-	0.4134
N	7.20	-	7.80	0.2835	-	0.3071
O	3.00	-	3.40	0.1181	-	0.1339

RECOMMENDED LAYOUT DRAWINGS




GBJ

OUTLINE DIMENSIONS						
Dim.	Milimeters			Inches		
	Min.	Typ.	Max.	Min.	Typ.	Max.
A	-	2.00	-	-	0.0787	-
B	-	2.00	-	-	0.0787	-
C	-	10.00	-	-	0.3937	-
D	-	4.60	-	-	0.1811	-
E	-	1.20	-	-	0.0472	-

GBJ50005 THRU GBJ5010
General Bridge Rectifiers



MARKING



MARKING INSTRUCTION

NH=Niuhan Trademark
 FF=Product Line Code,According To Actual Changes
 YWW=Date Code,According To Actual Changes
 LLWWF=Inernal Code,According To Actual Changes
 GBJ50xx=Model,xx=005,01,02,04,06,08,10

PACKING INFORMATION

Package Type	Package Code	Product Weight Approx(g/Pcs)	Package Method	Quantity (Pcs/Min. Pack.)	Quantity (Pcs/Inner Box)	Quantity (Pcs/Carton)
GBJ	P1	6.873	Box	250	250	2500
GBJ	P2	6.873	Tube	15	750	1500

GBJ50005 THRU GBJ5010


General Bridge Rectifiers



Recommended wave soldering condition

Product	Peak Temperature	Soldering Time
Pb-free devices	260 +0/-5 °C	5 +1/-1 seconds

Recommended temperature profile for IR reflow



Profile feature	Sn-Pb eutectic Assembly	Pb-free Assembly
Average ramp-up rate (T _{smax} to T _p)	3°C/second max.	3°C/second max.
Preheat -Temperature Min(T _{S min}) -Temperature Max(T _{S max}) -Time(t _{s min} to t _{s max})	100°C 150°C 60-120 seconds	150°C 200°C 60-180 seconds
Time maintained above: -Temperature (T _L) - Time (t _L)	183°C 60-150 seconds	217°C 60-150 seconds
Peak Temperature(T _P)	240 +0/-5 °C	260 +0/-5 °C
Time within 5°C of actual peak temperature(tp)	10-30 seconds	20-40 seconds
Ramp down rate	6°C/second max.	6°C/second max.
Time 25 °C to peak temperature	6 minutes max.	8 minutes max.

Note : All temperatures refer to topside of the package, measured on the package body surface.

GBJ50005 THRU GBJ5010

General Bridge Rectifiers



Disclaimer

- Reproducing and modifying information of the document is prohibited without permission from Nihang Electronics Technology Co., LTD
- Nihang Electronics Technology Co., LTD. reserves the rights to Making changes of the content herein the document anytime without notification.
- Nihang Electronics Technology Co., LTD. disclaims any and all liability arising out of the application or use of any product including damages incidentally and consequentially occurred.
- Nihang Electronics Technology Co., LTD. does not assume any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.
- Applications shown on the herein document are examples of standard use and operation. Customers are responsible in comprehending the suitable use in particular applications. Nihang Electronics Technology Co., LTD. Markings no representation or warranty that such applications will be suitable for the specified use without further testing or modification.
- The products shown herein are not designed and authorized for equipments requiring high level of reliability or relating to human life and for any applications concerning life-saving or life-sustaining, such as medical instruments, transportation equipment, aerospace machinery et cetera. Customers using or selling these products for use in such applications do so at their own risk and agree to fully indemnify Nihang Electronics Technology Co., LTD. for any damages resulting from such improper use or sale.
- When the appearance of the product and chip size does not change, in order to product the customer. quality, change the internal structure and the production process Nihang can not notify