



|         |                    |  |  |  |            |
|---------|--------------------|--|--|--|------------|
| EDITION | SUMMARY OF CHANGES |  |  |  | ISSUE DATE |
| A0      | 新版发行               |  |  |  | 2026/01/12 |



| STRUCTURE (构造) |                       |                     |           |        |
|----------------|-----------------------|---------------------|-----------|--------|
| NO.            | ITEM (项目)             | SPECIFICATION (规格)  |           |        |
| 1              | INSULATION (胶膜)       | 印字膜:通用版20624 (43μm) |           |        |
|                |                       | 白膜:80° C 60V (43μm) |           |        |
| 2              | SUPPORTING TAPE (补强板) | 225μm               | Blue (蓝色) |        |
| 3              | CONDUCTOR (导体)        | Thickness (厚度)      | 0.035     | ±0.005 |
|                |                       | Width (宽度)          | 0.3       | ±0.03  |
| 4              | CONDUCTOR (导体镀层)      | PLATED (电镀)         | 锡Sn (1μm) | MIN    |
|                |                       | PLATED (电镀)         |           |        |

| DIMENSION (尺寸)                 |    |                 |       |
|--------------------------------|----|-----------------|-------|
| No. of conductors (导体数目)       | N  | ( N ) P         |       |
| Pitch (间距)                     | P  | 0.5             | ±0.05 |
| Span (总间距)                     | SP | (N-1)*0.5       | ±0.05 |
| Width (总宽度)                    | W  | (N+1)*0.5       | ±0.08 |
| Margin (边缘宽度)                  | M  | 0.5             | ±0.07 |
| Total length (总长度)             | TL | (TL)            | ±2.0  |
| Insert Thickness (插接端厚度)       | T  | 0.3             | ±0.03 |
| Surface Thickness (线身厚度)       | ST | 0.12            | ±0.03 |
| Strip Length (裸铜长度)            | S1 | 4.0 4/3可定做      | ±0.5  |
|                                | S2 | 4.0 4/3可定做      | ±0.5  |
| Supporting Tape Length (补强板长度) | B1 | 6.0 8/6/5/4/可定做 | ±1.0  |
|                                | B2 | 6.0 8/6/5/4/可定做 | ±1.0  |

## 技术要求:

- 1、保存环境: 温度15~25℃ 湿 度: 30~50RH%
- 2、保质期: 镀金: 12个月 镀锡: 6个月
- 3、产品符合ROHS 2.0标准

|           |                                                                                       |                                                                                       |       |                                                                                                                                            |                                        |  |  |  |  |
|-----------|---------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------|-------|--------------------------------------------------------------------------------------------------------------------------------------------|----------------------------------------|--|--|--|--|
| DESIGN:   | Xiping Huang                                                                          |                                                                                       |       |                                                       | 广东国连电子有限公司                             |  |  |  |  |
| CHECK:    | Ke Tian                                                                               |                                                                                       |       |                                                                                                                                            | GUANGDONG GUOLIAN ELECTRONICS CO., LTD |  |  |  |  |
| APPROVED: | Youquan Xu                                                                            |                                                                                       |       | TITLE: FFC CABLE B型                                                                                                                        |                                        |  |  |  |  |
| DIM       | TOL                                                                                   |  | TOL   | PART NO. 0.5*NP*TL*B(3/3/5/5) (0.035*0.3)                                                                                                  |                                        |  |  |  |  |
| X.        | ±0.25                                                                                 |                                                                                       |       |                                                                                                                                            |                                        |  |  |  |  |
| X. X      | ±0.20                                                                                 | X°                                                                                    | ±3.0° | REV. A      SCALE: N/A      UNIT: mm      SHEET: 1/1  |                                        |  |  |  |  |
| X. XX     | ±0.15                                                                                 | X. X°                                                                                 |       |                                                                                                                                            |                                        |  |  |  |  |
| X. XXX    |  | X. XX°                                                                                |       |                                                                                                                                            |                                        |  |  |  |  |
|           |                                                                                       | X. XXX°                                                                               |       |                                                                                                                                            |                                        |  |  |  |  |