









F		F		F	
修订 REV	标记 MARK	修改摘要 REVISION DESCRIPTION	签名 SIGNATURE	日期 DATE	
A0		NEW RELEASE	黄艳兰	2021-05-10	



PCB LAYOUT(Tolerance:±0.05)



Specifications:

Poles: 02 to 16

Contact resistance: $\leq 20\text{m}\Omega$

Insulation resistance: $\geq 500\text{M}\Omega$

Rated voltage:100V AC DC

Rated current:2.0A AC DC

Withstand Voltage: 500V AC/minute

Temperature Range: $-25^{\circ}\text{C} \sim +85^{\circ}\text{C}$

Housing:PA9T UL94V-0,Natural

Contacts: Phosphor Bronze/ Sn-plated

Solder tabs:Brass/ Sn-plated

PIN.	DIM A	DIM B	PIN.	DIM A	DIM B
2pin	1.50	7.50	10pin	13.50	19.50
3pin	3.00	9.00	*11pin	15.00	21.00
4pin	4.50	10.50	*12pin	16.50	22.50
5pin	6.00	12.00	*13pin	18.00	24.00
6pin	7.50	13.50	*14pin	19.50	25.50
7pin	9.00	15.00	*15pin	21.00	27.00
8pin	10.50	16.50	*16pin	22.50	28.50
9pin	12.00	18.00			

包装数量：每盘装600PCS。

Circuits	DIM. D	DIM. E	Q'ty/Reel	Packing (Reel/Carton)
02~05PIN	11.5	24	600PCS	15/Reel



深 圳 市 华 德 共 创 科 技 有 限 公 司

Shenzhen Huade co-create Technology Co.,LTD

电话：0755-27111216 传真：0755-29940187

-TOLERANCES- UNLESS OTHERWISE SPECIFIED 公差参数表						TITLE: 产品名称：ZE1.5立贴			
X.X	±0.30	X.X°	±3°	APPD: 核准：谢亮	PART NO: 产品编号：HDGC1501WVD-S-XP				
X.XX	±0.30	X.XX°	±2°	CHECK: 校对：王建业	DATE	SCALE	UNIT	CODE NUMBER	
X.XXX	±0.10	X.XXX°	±1°	DRAW: 绘图：黄艳兰	2021-05-10	1:1	mm	A018	