

1



2

3

4

This document contains proprietary information and such information may not be disclosed to others for any purposes,
not used for sales/marketing/procurement purposes without written permission

REV	DESCRIPTION OF REVISION	ECN NO.	BY	DATE	APPROVED
A	Initial Release	—	H.wei	12/7/06	12/7/06



技术特性/Electrical Specifications

特性阻抗/Impedance	50 Ω
频率范围/Frequency Range	DC-18GHz
电压驻波比/VSWR	≤ 1.30
插入损耗/Insert Loss	$\leq 0.05 \text{xsqt. (f GHz)} \text{dB}$
耐压/Withstanding Voltage	$\geq 500\text{V}$
绝缘电阻/Insulation Resistance	$\geq 5000\text{M}\Omega$

材料/Material Data

外导体/Outer contact	铍青铜 Beryllium Bronze/金 gold Plated
中心导体/Center contact	铍青铜 Beryllium Bronze/金 gold Plated
绝缘介质/Insulator	聚四氟乙烯/PTFE


连接参数/The connection parameters

耐久性/durability	≥ 500 次 (cycles)
----------------	-----------------------

环境参数/Environmental Data

温度范围/Temperature Range	-55℃ to 125℃
------------------------	--------------

推荐安装开孔尺寸



Notes:

- ALL SPECIFICATIONS ARE SUBJECT TO CHANGE NOTICE AT ANY TIME
- CUSTOMER OUTLINE DRAWING FOR REFERENCE ONLY

DRAWN: H.wei 12/07/06

ENGINEER: L.yu 12/07/06

APPROVED: W.yi 12/07/06

TOLERANCES UNLESS OTHERWISE SPECIFIED

X ± 0.50

.X ± 0.20

.XX ± 0.10

ANGLES $\pm 1^\circ$

TITLE:

RF Coaxial Connector

SMP Female Flange For PCB

PART NO: HL3-SMP-KHD092



DIMENSION IN MILLIMETERS (mm)

SIZE: A4

SCALE: N/A

SHEET: 1/1

REV: A