




修订 REV	标记 MARK	修改摘要 REVISION DESCRIPTION	签名 SIGNATURE	日期 DATE
A0		NEW RELEASE	黄艳兰	2021-05-10

Specifications:
Poles: 02 to 16
Contact resistance:≤20mΩ
Insulation resistance:≥500MΩ
Rated voltage:100V AC DC
Rated current:2.0A AC DC
Withstand Voltage: 500V AC/minute
Temperature Range:-25℃~ +85℃
Housing:PA9T UL94V-0,Natural
Contacts:PhosphorBronze/ Sn-plated
Solder tabs:Brass/ Sn-plated

Circuits	DIM. D	DIM. E	Q'ty/Reel	Packing (Reel/Caton)
02~05PIN	-	24	800PCS	15/Reel

PIN.	DIM A	DIM B	PIN.	DIM A	DIM B
2pin	1.50	7.50	10pin	13.50	19.50
3pin	3.00	9.00	11pin	15.00	21.00
4pin	4.50	10.50	12pin	16.50	22.50
5pin	6.00	12.00	13pin	18.00	24.00
6pin	7.50	13.50	14pin	19.50	25.50
7pin	9.00	15.00	15pin	21.00	27.00
8pin	10.50	16.50	16pin	22.50	28.50
9pin	12.00	18.00			

包装数量：每盘装800PCS。

HDGC 深圳市华德共创科技有限公司 Shenzhen Huade co-create Technology Co.,LTD 电话：0755-27111216 传真：0755-29940187				TITLE: 产品名称：ZE1.5卧贴			
X.X ±0.30		X.X° ±3°		PART NO: 产品编号：HDGC1501WRD-S-XP			
X.XX ±0.30		X.XX° ±2°		DATE	SCALE	UNIT	CODE NUMBER
X.XXX ±0.10		X.XXX° ±1°		2021-05-10	1:1	mm	A018