

Features

- Wide supply voltage range from 0.8V to 2.7V
- Inputs accept voltages up to 3.6V
- I_{OFF} supports partial-power-down mode
- Low static power consumption; $I_{CC}=0.5\mu A$ (Max.)
- ESD Protection Exceeds JESD 22
 - 2000-V Human-Body Model (A114-A)
 - 200-V Machine Model (A115-A)
 - 1000-V Charged-Device Model (C101)

General Description

The is a single bus buffer/line driver with 3-state output. When the output enable (OE) is high the output will be disabled. In contrast, when the OE is low, true data will pass from A input to the Y output.

Applications

- AV Receiver
- Audio Dock:Portable
- Blu-ray Player and Home Theater
- Embedded PC
- Personal Digital Assistant(PDA)
- Power:Telecom/Server AC/DC Supply:Single Controller:Analog and Digital
- Solid State Drive(SSD):Client and Enterprise
- Wireless Headset,Keyboard,and Mouse


Logic Diagram



Ordering Information

ORDER NUMBER	PACKAGE DESCRIPTION	PACKAGE OPTION
SN74AUC1G126DCKR-TP	SOT353	Tape and Reel,3000

Pin Configuratio (TOP VIEW)



SOT353

Function Table (each gate)

INPUT(OE)	INPUT(A)	OUTPUT(Y)
H	H	H
H	L	L
L	X	Z

H: HIGH voltage level; L: LOW voltage level;
X=don't care; Z=high-impedance OFF-state.

Absolute Maximum Ratings

PARAMETER	SYMBOL	CONDITIONS	RATINGS	UNIT
Supply Voltage	V _{CC}		-0.5 ~ +3.6	V
Input Voltage	V _{IN}		-0.5 ~ +3.6	V
Output Voltage	V _{OUT}	Output in the high or low state	-0.5 ~ +V _{CC} +0.5V	V
		Output in the power-off state	-0.5 ~ +3.6	V
VCC or GND Current	I _{CC}		±50	mA
Continuous Output Current	I _{OUT}	V _{OUT} =0~V _{CC}	±20	mA
Input Clamp Current	I _{IK}	V _{IN} <0	-50	mA
Output Clamp Current	I _{OK}	V _{OUT} <0	-50	mA
Storage Temperature Range	T _{STG}		-65 ~ +150	°C
Junction to Ambient	θ _{JA}	SOT353	280	°C/W

Note: Absolute maximum ratings are those values beyond which the device could be permanently damaged. Absolute maximum ratings are stress ratings only and functional device operation is not implied.

Recommended Operating Conditions

PARAMETER	SYMBOL	TEST CONDITIONS	MIN	TYP	MAX	UNIT
Supply Voltage	V _{CC}	Operating	0.8	--	2.7	V
Input Voltage	V _{IN}		0	--	2.7	V
Output Voltage	V _{OUT}	High or low state	0	--	V _{CC}	V
Input Transition Rise or Fall Rate	Δt/Δv	V _{CC} =0.8V ~ 2.7V	--	--	200	ns/V
Operating Temperature	T _A		-40	--	+125	°C

SN74AUC1G126DCKR-TP

SINGLE BUS BUFFER GATEWITH 3-STATE OUTPUT

WWW.TECHPUBLIC.COM

Electrical Characteristics (T_A=25°C ,unless otherwise specified)

PARAMETER	SYMBOL	TEST CONDITIONS	MIN	TYP	MAX	UNIT
High-level Input Voltage	V _{IH}	V _{CC} =0.8V	0.7×V _{CC}	--	--	V
		V _{CC} =0.9V ~ 1.95V	0.65×V _{CC}	--	--	V
		V _{CC} =2.3V ~ 2.7V	1.6	--	--	V
Low-level Input Voltage	V _{IL}	V _{CC} =0.8V	--	--	0.3×V _{CC}	V
		V _{CC} =1.1V ~ 1.95V	--	--	0.35×V _{CC}	V
		V _{CC} =2.3V ~ 2.7V	--	--	0.7	V
High-Level Output Voltage	V _{OH}	V _{CC} =0.8 ~ 2.7V, I _{OH} =-20μA	V _{CC} -0.1	--	--	V
		V _{CC} =1.1V, I _{OH} =-1.1mA	0.75×V _{CC}	--	--	V
		V _{CC} =1.4V, I _{OH} =-1.7mA	1.11	--	--	V
		V _{CC} =1.65V, I _{OH} =-1.9mA	1.32	--	--	V
		V _{CC} =2.7V	I _{OH} =-2.3mA	2.05	--	V
			I _{OH} =-3.1mA	1.9	--	V
Low-Level Output Voltage	V _{OL}	V _{CC} =0.8 ~ 2.7V, I _{OL} =20μA	--	--	0.1	V
		V _{CC} =1.1V, I _{OL} =1.1mA	--	--	0.3×V _{CC}	V
		V _{CC} =1.4V, I _{OL} =1.7mA	--	--	0.31	V
		V _{CC} =1.65V, I _{OL} =1.9mA	--	--	0.31	V
		V _{CC} =2.7V	I _{OL} =2.3mA	--	0.31	V
			I _{OL} =3.1mA	--	0.44	V
Input Leakage Current	I _{I(LEAK)}	V _{CC} =0 ~ 2.7V, V _{IN} =GND ~ 2.7V	--	--	±0.1	μA
Power OFF Leakage Current	I _{off}	V _{CC} =0 V, V _{IN} or V _{OUT} =0 ~ 2.7V	--	--	±0.2	μA
Additional Power OFF Leakage Current	ΔI _{off}	V _{CC} =0 V~0.2V, V _{IN} or V _{OUT} =0 ~ 2.7V	--	--	±0.2	μA
Quiescent Supply Current	I _{CC}	V _{CC} =0.8 ~2.7V, V _{IN} =V _{CC} or GND, I _{OUT} =0	--	--	0.5	μA
Additional Quiescent Supply Current Per Input Pin	ΔI _{CC}	V _{CC} =2.7 V, V _{IN} =V _{CC} -0.6V, I _{OUT} =0	--	--	40	μA
Input Capacitance	C _I	V _{CC} =0V-2.7V, V _{IN} =V _{CC} or GND	--	1.5	--	pF
Output Capacitance	C _{OUT}	V _{CC} =0V, V _{OUT} =GND	--	3.0	--	pF

SN74AUC1G126DCKR-TP

SINGLE BUS BUFFER GATEWITH 3-STATE OUTPUT

WWW.TECHPUBLIC.COM


OPERATING CHARACTERISTICS (f=10MHz, TA =25°C , unless otherwise specified)

PARAMETER	SYMBOL	TEST CONDITIONS	MIN	TYP	MAX	UNIT
Power Dissipation Capacitance	C _{PD}	V _{CC} =0.8V	--	3.8	--	pF
		V _{CC} =1.2±0.1V	--	3.7	--	pF
		V _{CC} =1.5±0.1V	--	3.7	--	pF
		V _{CC} =1.8±0.15V	--	3.7	--	pF
		V _{CC} =2.5±0.2V	--	3.9	--	pF

SWITCHING CHARACTERISTICS (TA =25°C, unless otherwise specified)

PARAMETER	SYMBOL	TEST CONDITIONS	MIN	TYP	MAX	UNIT
Propagation delay from inputs (A) to output(Y)	t _{PD}	CL=5pF, RL=1MΩ	V _{CC} =0.8V	--	18.1	ns
			V _{CC} =1.2±0.1V	4.3	7.4	ns
			V _{CC} =1.5±0.1V	3.3	5.2	ns
			V _{CC} =1.8±0.15V	2.6	4.1	ns
			V _{CC} =2.5±0.2V	2	2.9	ns
		CL=10pF, RL=1MΩ	V _{CC} =0.8V	--	20.5	ns
			V _{CC} =1.2±0.1V	4.6	8.4	ns
			V _{CC} =1.5±0.1V	3.5	5.9	ns
			V _{CC} =1.8±0.15V	3.9	4.7	ns
			V _{CC} =2.5±0.2V	2.3	3.4	ns
		CL=15pF, RL=1MΩ	V _{CC} =0.8V	--	22.5	ns
			V _{CC} =1.2±0.1V	5.8	9.3	ns
			V _{CC} =1.5±0.1V	4.4	6.6	ns
			V _{CC} =1.8±0.15V	3.5	5.3	ns
			V _{CC} =2.5±0.2V	2.7	3.9	ns
		CL=30pF, RL=1MΩ	V _{CC} =0.8V	--	29	ns
			V _{CC} =1.2±0.1V	7.4	12	ns
			V _{CC} =1.5±0.1V	5.7	8.6	ns
			V _{CC} =1.8±0.15V	4.8	6.9	ns
			V _{CC} =2.5±0.2V	3.9	5.1	ns


TEST CIRCUIT AND WAVEFORMS




TEST	S
t_{PLH}/t_{PHL}	Open
t_{PHZ}/t_{PZH}	GND
t_{PLZ}/t_{PZL}	$2 \times V_{CC}$

TEST CIRCUIT

V_{CC}	V_{IN}	t_R / t_F	V_M	V_{LOAD}	C_L	R_L	V_{Δ}
0.8	V_{CC}	3ns	$V_{CC}/2$	$2 \times V_{CC}$	5,10,15,30pF	5k Ω	0.1V
$1.2 \pm 0.1V$	V_{CC}	3ns	$V_{CC}/2$	$2 \times V_{CC}$	5,10,15,30pF	5k Ω	0.1V
$1.5 \pm 0.1V$	V_{CC}	3ns	$V_{CC}/2$	$2 \times V_{CC}$	5,10,15,30pF	5k Ω	0.1V
$1.8 \pm 0.15V$	V_{CC}	3ns	$V_{CC}/2$	$2 \times V_{CC}$	5,10,15,30pF	5k Ω	0.15V
$2.5 \pm 0.2V$	V_{CC}	3ns	$V_{CC}/2$	$2 \times V_{CC}$	5,10,15,30pF	5k Ω	0.15V



PROPAGATION DELAY TIMES




ENABLE AND DISABLE TIMES

Notes:

1. C_L includes probe and jig capacitance.
2. All input pulses are supplied by generators having the following characteristics: $PRR \leq 10MHz$, $Z_O = 50\Omega$.

Package informantion (Unit: mm)

SOT353



Mounting Pad Layout (unit: mm)

