









SPECIFICATION

1. Rating : DC 20V 5A;
2. Contact resistance: $\leq 0.03 \Omega$;
3. Insulation resistance: $\geq 100M \Omega$ (DC250V);
4. Withstand voltage: 500VAC ;
5. Insertion and extraction force: 3-40N;
6. life test: 5,000 cycles.



6	CONTACT FOOT	1	BRASS	Ag-Plating
5	CONTACT FOOT	1	SUS301	Ni-Plating
4	STOPPER	1	SUS301	—
3	PIN	1	BRASS	Ni-Plating
2	SPRING PIECE	1	BRONZE	Ag-Plating
1	HOUSING	1	PA9T	—
NO.	DESCRIPTION	QTY	MATERIAL	PLATING

							ANGLE	±5°	Designed:	Checked:	Approved:	Date: 2022/4/23	MODEL TYPE: DC JACK	
							30 ~	±0.30					PART NO. CAX-DC-3035-2.0-5A-XL	
							10 ~ 30	±0.20	浙江创都电子科技有限公司				UNIT: SCALE: VIEW: Edition	
—	A/O		NEW	——	——	——	~ 10	±0.10					mm 1:1  B	
ECN NO	REV	DATE	DESCRIPTION	CHANGE	CHECK	APPRO.	UNSPECIFIED TOLERANCE							
1							4		5	6	7	8	9	10