




REV.	ECN NO.	MODIFIED MARK	APPROVED
A		First release	Frank.Lei



711-0003-0076

STEM
0: PC
1: PA66


SERIAL NUMBER

OPERATING FORCE
1: 160±50gf
2: 200±50gf
3: 260±50gf


COVER
0: SUS430
1: Cu

SPRING
0: PHOSPHOR BRONZE
1: SUS301



ELECTRICAL:
1.RATED CURRENT: 50 mA Max.
2.RATED VOLTAGE: 12V DC.
3.CONTACT RESISTANCE: 30 MILLIOHMS Max.
4.INSULATION RESISTANCE: 100 MEGAOHMS Min.
5.DIELECTRIC WITHSTANDING VOLTAGE: 250V AC Min.
MECHANICAL:
1.DURRABILITY: 100000 CYCLES Min.
ENVIRONMENTAL:
1.TEMPERATURE RANGE: -20°C TO 70°C.



Circuit Diagram



P.C.B Holes Diagram
BOTTOM VIEW



5	COVER	1	SUS430/H62(CuSn-PLATED)		RoHS COMPLIANT
4	SPRING	1	PHOSPHOR BRONZE/SUS301	COATING SILVER	
3	CONTACT TERMINAL	1	BRASS	Ag-PLATED	
2	STEM	1	PA66/PC	BLACK	
1	HOUSING	1	PA66	BLACK	
No.	P/N	Q'TY	Material	Finish/Colour	Remarked
X.	±0.35	X.* ±5°	MODEL NAME: (PART NO.)		浙江创都电子科技有限公司
.X	±0.25	.X* ±3°			
.XX	±0.20	.XX* ±1°	MAT'L: See Detail Sheet	DESIGN: 10/24'18	TITLE: CAX-TS-1102S-6x6x9.5DDFT
.XXX	±0.15	TOL TABLE:	FINISH: See Detail Sheet	CHECKED: 0/24'18	
			Q'TY 1	APPROVED: 10/24'18	UNIT: MM
					VIEW: -
					SCALE: 5:1
					SHEET: 1/1
					SIZE: A3