










REV.	ECN NO.	MODIFIED MARK	APPROVED
A		FIRST RELEASE	



NUT




WASHER



仅供参考

NOTES:
ELECTRICAL:
1: RATED CURRENT: 1A Max.
2: RATED VOLTAGE: 50V AC.
3: CONTACT RESISTANCE: 100 MILLIOHMS Max.
AFTER TESTING: 100 MILLIOHMS Max.
4: INSULATION RESISTANCE: 100 MEGAOHMS Min.
5: DIELECTRIC WITHSTANDING VOLTAGE: 500 VAC Min.
MECHANICAL:
1: INSERTION FORCE: 5N-40N.
2: WITHDRAWAL FORCE: 5N-40N.
3: DURRABILITY: 5000 CYCLES.
ENVIRONMENTAL:
TEMPERATURE RANGE: -20°C TO 60°C.



SCHEMATIC

⑧	WASHER-B	1	STEEL t=0.7	Ni PLATED	RoHS 2.0			
⑦	NUT	1	BRASS	Ni PLATED				
⑥	WASHER-A	1	STEEL	Ni PLATED				
⑤	SOCKET	1	BRASS	Ni PLATED				
④	TERMINAL-C	1	BRASS t=0.4	Ag PLATED				
③	TERMINAL-B	1	BRONZE t=0.4	Ag PLATED				
②	TERMINAL-A	1	BRASS t=0.4	Ag PLATED				
①	HOUSE	1	PA66	BLACK				
NO.	PART NAME	Q'TY	MATERIAL	FINISH/COLOR	REMARK			
ANGLE		±5°		MODEL NAME: CAX-PJ-6347D-6P-HP (PART NO.) 浙江创都电子科技有限公司				
63 < L		±0.5						
16 < L ≤ 63		±0.4						
4 < L ≤ 16		±0.3						
L ≤ 4		±0.2						
TOL TABLE:		MAT'L: See table	DESIGN:	TITLE: 6.35 PHONE JACK				
		FINISH: See table	CHECKED:	DWG NO.:		REV.: A		
		Q'TY: /	APPROVED:	UNIT: mm	VIEW: 	SCALE: 5:1	SHEET: 1/1	SIZE: A3