





REV.	ECN NO.	MODIFIED MARK	APPROVED
B			



COLOR TABLE

CODE	A	B
COLOR	WHITE	RED



SCHEMATIC

NOTES:

ELECTRICAL:

1:RATED CURRENT: 1A Max.

2:RATED VOLTAGE: 12V DC.

3:CONTACT RESISTANCE: 30 MILLIOHMS Max.

AFTER TESTING:100 MILLIOHMS Max.

4:INSULATION RESISTANCE: 100 MEGAOHMS Min.

5:DIELECTRIC WITHSTANDING VOLTAGE: 500 VAC Min.

MECHANICAL:

1:INSERTION FORCE: 3N-30N.

2:WITHDRAWAL FORCE: 3N-30N.

3:DURRABILITY: 500 CYCLES.

ENVIRONMENTAL:

TEMPERATURE RANGE: -20°C TO 60°C.

MARK"▼"AS THE KEY CONTROL SIZE.

PIN POSITION AND SIZE OK IF FIT PCB BOARD

⑤	TERMINAL	2	BRASS t=0.5	CuSn PLATED	RoHS 2.0						
④	SOCKET	2	BRASS	CuSn PLATED							
③	COVER	1	ABS	BLACK							
②	WASHER	2	ABS	SEE COLOR TABLE							
①	HOUSE	1	ABS	WHITE							
NO.	PART NAME		Q'TY	MATERIAL	FINISH/COLOR	REMARK					
ANGLE		±5°	MODEL NAME: (PART NO.) CAX-AV-210-WR-PHP		浙江创都电子科技有限公司						
63 < L		±0.5									
16 < L ≤ 63		±0.4									
4 < L ≤ 16		±0.3									
L ≤ 4		±0.2	MAT'L: See table	DESIGN: 11/13'24	TITLE: RCA PIN JACK						
TOL TABLE:		FINISH: See table						CHECKED: 11/13'24	DWG NO.:		REV.: B