






- SPECIFICATION**
- 1. Rating : DC 24V 3A;
 - 2. Contact resistance: $\leq 0.03\Omega$;
 - 3. Insulation resistance: $\geq 100M\Omega$ (DC250V);
 - 4. Withstand voltage: 500VAC ;
 - 5. Insertion and extraction force: 3-40N;
 - 6. life test: 5,000 cycles.




MATE PLUG

环保
Green Product



CIRCUIT DIAGRAM



PCB Holes diagram
Bottom View

4	SHUNT TERMINAL	3	1	BRASS	Sn-Plated
3	TIP SPRING	2	1	PHOSPHOR BRONZE	Sn-Plated
2	CENTER PIN	1	1	BRASS	Sn-Plated
1	HOUSING		1	PBT	Black
NO.	PART NAME	TER.NO.	QT*Y	MATERIAL	REMARK
DSND		DATE		SCAL: 1:1	NAME: DC JACK
CHKD		DATE		VIEW:	CAT.NO: CAX-DC-108-1.2-10A-XL
APVD		DATE		UNIT:	
浙江创都电子科技有限公司				DWG.NO. DC-108-1.2-10A-XL	REVISED B/O

△ X					Angle	±5°
△ X					63 < L	±0.5
△ X					16 < L ≤ 63	±0.50
△ X					4 < L ≤ 16	±0.35
REMARK	EXCHANGE DESCRIPTION	DATE	REVISED	APVD	L ≤ 4	±0.25
REVISIONS					UNLESS TOLERANCE	