

MATERIAL:

1. HOUSING MATERIAL :GLASS FILLED POLYESTER UL94V-0.
2. CONTACT MATERIAL :PHOSPHOR BRONZE t=0.30mm.
3. PLATING :SELECTING GOLD PLATING 3u"~50u" OVE
NICKEL

ELECTRICAL:

1. VOLTAGE RATING :125 VAC RMS.
2. CURRENT RATING :1.5 AMP.
3. CONTACT RESISTANCE :30 MILLIOHMS MAX.
4. INSULATION RESISTANCE :500 MEGOHMS MIN @ 500V DC .
5. DIELECTRIC WITHSTANDING RESISTANCE
:1000V AC RMS 50Hz. 1MIN.

MECHANICAL:


1. DURRABILITY: :750 CYCLES MIN.
2. PCB RETENTION PRE-SOLDER :1 LB MIN.

ENVIRONMENTAL:

1. STORAGE : -40° C TO 85° C.
2. OPERATION : 0° C TO 70° C.



深圳市华宇创精密电子有限公司

TOLERANCE:		DRAWN BY : 陈一鸣	DATE : 2014-02-23	PART NAME: RJ45 180 ° DIP 1X2无灯带屏蔽	
X.X ±0.30 X.XX ±0.25 X.XXX ±0.15 X.' ±2" X.X' ±0.5"					
 UNIT: mm [inch]		CHECKED BY:	DATE :	PART NO.	HYCW222-RJ45-156B
		马跃	2014-02-23	MOLD NO.	
SCALE:1:1 SIZE: A4		APPROVED BY:	DATE :	DRAW NO:	HYC-1801071805
		柯南	2014-02-23	SHEET NO.	1 OF 1