

This document contains proprietary information and such information may not be disclosed to others for any purposes,
not used for sales/marketing/procurement purposes without written permission

REV	DESCRIPTION OF REVISION	ECN NO.	BY	DATE	APPROVED
A	Initial Release	—	H.wei	19/03/17	19/03/17

1 Electrical


1.1 Impedance	50 Ω
1.2 Frequency	0~18GHz
1.3 Dielectric withstanding voltage	1000V(volts RMS)
1.4 Center contact resistance	$\leq 3\text{M}\Omega$
1.5 Outer contact resistance	$\leq 2\text{M}\Omega$
1.6 Insulation resistance:	$\geq 5000\text{M}\Omega$

2 Environmental&Mechanical


2.1 Temperature range	-45℃~125℃
2.2 RoHs Compliant	
2.3 Durability	>500 cycles

3 Materials&plating

3.1 Body:	Brass, Gold plated
3.2 Insulator:	Teflon
3.3 Contact Pin:	Beryllium Copper Gold plated



Recommended PCB Layout



Notes:

- ALL SPECIFICATIONS ARE SUBJECT TO CHANGE NOTICE AT ANY TIME
- CUSTOMER OUTLINE DRAWING FOR REFERENCE ONLY

DRAWN: H.wei 19/03/17
ENGINEER: L.yu 19/03/17
APPROVED: W.yi 19/03/17
TOLERANCES UNLESS OTHERWISE SPECIFIED
X ± 0.50
.X ± 0.20
.XX ± 0.10
ANGLES $\pm 1^\circ$

TITLE:
RF Coaxial Connector
SMA Female Right Angle
Conn. For PCB Mount

PART NO: HL-SMA-KWHD



DIMENSION IN MILLIMETERS (mm)

SIZE: A4	SCALE: N/A	SHEET: 1/1	REV: A
----------	------------	------------	--------