





NOTES:

MATERIAL:

1. HOUSING MATERIAL : GLASS FILLED POLYESTER UL94V-0.
2. CONTACT MATERIAL : PHOSPHOR BRONZE $\phi = 0.46\text{mm}$.
3. PLATING : SELECTING GOLD PLATING $3\mu\text{m} \sim 50\mu\text{m}$ OVER NICKEL

ELECTRICAL:

1. VOLTAGE RATING : 125 VAC RMS.
2. CURRENT RATING : 1.5 AMP.
3. CONTACT RESISTANCE : 30 MILLIOHMS MAX.
4. INSULATION RESISTANCE : 500 MEGOHMS MIN @ 500V DC .
5. DIELECTRIC WITHSTANDING RESISTANCE : 1000V AC RMS 50Hz. 1MIN.

MECHANICAL:

1. DURABILITY : 750 CYCLES MIN.
2. PCB RETENTION PRE-SOLDER : 1 LB MIN.

ENVIRONMENTAL:

1. STORAGE : -40°C TO 85°C .
2. OPERATION : 0°C TO 70°C .



深圳市华宇创精密电子有限公司

TOLERANCE: X.X ± 0.30 X.XX ± 0.25 X.XXX ± 0.15 X' $\pm 2'$ X.X' $\pm 0.5'$	DRAWN BY : 陈一鸣	DATE : 2014-02-23	PART NAME: RJ45 180° DIP 1X4	
	CHECKED BY: 马跃	DATE : 2014-02-23	PART NO.	HYCW272-RJ45-156B
 UNIT: mm [inch] SCALE: 1:1 SIZE: A4	APPROVED BY: 柯南	DATE : 2014-02-23	MOLD NO.	
			DRAW NO:	HYC-1812061516
			SHEET NO.	1 OF 1