






PC BOARD LAYOUT  
THICKNESS=1.6MM

#### NOTES:

##### ELECTRICAL:

1. VOLTAGE RATING : 125 VAC RMS.
2. CURRENT RATING : 1.5 AMP.
3. CONTACT RESISTANCE : 45 MILLIOHMS MAX.
4. INSULATION RESISTANCE : 1000 MEGOHMS MIN @ 500 VDC
5. DIELECTRIC STRENGTH : 1000 V AC OR 1500V DC RMS  
@ 0.5mA 50 Hz / 60 Hz 1 Minute

##### MECHANICAL:

1. HOUSING&INSERT& MATERIAL : PBT UL94V-0. COLOR BLACK
2. CONTACT MATERIAL : PHOSPHOR BRONZE T=0.35mm.
3. PLATING : 1: CONTACT AREA- SELECTIVE GOLD PLATING.  
2: TAILS PLATING TIN OVER NICKEL.
4. OPERATING LIFE : 750 CYCLES MIN.
5. MATING/UNMATING FORCE: : 22N / 2.27kg Max.
6. RETENTION STRENGTH: : 57.83N Min.



深圳市华宇创精密电子有限公司

#### TOLERANCE:

X.X ±0.30  
X.XX ±0.25  
X.XXX ±0.15

X' ±2" X.X' ±0.5'



UNIT: mm [inch]

SCALE:1:1 SIZE: A4

DRAWN BY :

陈一鸣

DATE :

2014-02-23

PART NAME:

RJ11 90 ° DIP 4P4C 有耳

CHECKED BY:

马跃

DATE :

2014-02-23

PART NO.

HYCW19-RJ11-206B

MOLD NO.

APPROVED BY:

柯南

DATE :

2014-02-23

DRAW NO:

HYC-RJ19092118

SHEET NO.

1 OF 1