

3D VIEW

Electrical Characteristics :
Insulation Resistance : 500MΩ Min.
Contact Resistance : 50mΩ Max.
Withstand Voltage : 1000 VAC 1 minute.
Current Rating : 1.5A

Material:





Housing: Thermoplastic UL 94V-0

Contact : Selective Gold Plating

Terminal: 0.25mm Thickness Copper Alloy
Plated With Gold And Tin In Solder Area.


Shell: Alloy ,Nickel Plating

Fork:Alloy



W/LED RECOMMENDED PCB LAYOUT
COMPONENT SIDE(t=1.6mm, tol:±0.05)

LED ELECTRICAL CHARACTERISTIC



Standard LED	Wavelength	Forward V (Min/Max)	Forward A	Type
Green	568nm	1.8V/2.8V	20mA	squareness
Yellow	585nm	1.8V/2.8V	20mA	squareness



深圳市华宇创精密电子有限公司

TOLERANCE: X.X ±0.30 X.XX ±0.25 X.XXX ±0.15 X.' ±2" X.X' ±0.5"	DRAWN BY : 陈一鸣	DATE : 2014-02-23	PART NAME: RJ45 90° DIP 沉板带灯	
	CHECKED BY: 马跃	DATE : 2014-02-23	PART NO. HYCW261-RJ45-295B	MOLD NO.
 UNIT: mm [inch] SCALE:1:1 SIZE: A4	APPROVED BY: 柯南	DATE : 2014-02-23	DRAW NO: HYC-RJ19111528	SHEET NO. 1 OF 1