


Product Summary

- V_{DS} 20 V
- I_{DS} ($V_{GS}=4.5V$) 2.5 A
- $R_{DS(ON)}$ ($V_{GS}=4.5V$) $\leq 100m\Omega$

Package and Pin Configuration

Bottom View




DFN1006-3

Application

- Interfacing Switching
- DC-DC Converters
- Power management functions

Circuit diagram

Top View



Absolute Maximum Ratings ($T_A=25^\circ C$ unless otherwise noted)

PARAMETER	SYMBOL	LIMIT	UNIT
Drain-Source Voltage	V_{DS}	20	V
Gate-Source Voltage	V_{GS}	± 12	V
Continuous Drain Current $T_A=25^\circ C$	I_D	2.5	A
Continuous Drain Current $T_A=70^\circ C$	I_D	1.8	A
Pulsed Drain Current ($t = 100 \mu s$)	I_{DM}	10	A
Maximum Power Dissipation $T_A=25^\circ C$	P_D	0.715	W
Operating Junction Temperature Range	T_J	-55 to +150	$^\circ C$
Storage Temperature Range	T_{stg}	-55 to +150	$^\circ C$

Thermal Characteristic

PARAMETER	Symbol	Value	Unit
Thermal Resistance from Junction to Ambient($t \leq 10s$)	$R_{\theta JA}$	175	$^\circ C/W$

Note : When mounted on 1" square PCB (FR4 material).





Electrical Characteristics (T_A=25°C unless otherwise noted)

PARAMETER	CONDITIONS	SYMBOL	MIN	TYP	MAX	UNIT
Characteristics						
Drain-Source Breakdown Voltage	$V_{GS}=0V, I_D=10\mu A$	BV_{DSS}	20	--	--	V
Gate-Source Threshold Voltage	$V_{DS}=V_{GS}, I_D=250\mu A$	$V_{GS(th)}$	0.45	0.75	0.9	V
Gate-Source Leakage	$V_{DS}=0V, V_{GS}=\pm 12V$	I_{GSS}	--	--	± 100	nA
Zero Gate Voltage Drain Current	$V_{DS}=20V, V_{GS}=0V$	I_{DSS}	--	--	1.0	μA
Drain-Source On-State Resistance (Note 1)	$V_{GS}=4.5V, I_D=1A$	$R_{DS(on)}$	--	88	100	m Ω
	$V_{GS}=2.5V, I_D=1A$		--	95	110	
Forward Transconductance (Note 2)	$V_{DS}=2V, I_D=1A$	g_{fs}	--	6	--	S
Dynamic (Note 2)						
Input Capacitance	$V_{DS}=10V, V_{GS}=0V,$ $F=1.0MHz$	C_{iss}	--	135	--	pF
Output Capacitance		C_{oss}	--	16	--	
Reverse Transfer Capacitance		C_{rss}	--	19	--	
Switching						
Turn-On Delay Time (Note 3)	$V_{DS}=10V,$ $V_{GS}=4.5V,$ $I_D=1A,$ $R_G=6\Omega.$	$t_{d(on)}$	--	9.0	--	nS
Rise Time (Note 3)		t_r	--	23	--	
Turn-Off Delay Time (Note 3)		$t_{d(off)}$	--	38	--	
Fall Time (Note 3)		t_f	--	3.0	--	
Total Gate Charge	$V_{DS}=10V,$ $I_D=1A,$ $V_{GS}=4.5V$	Q_g	--	2.2	--	nC
Gate Source Charge		Q_{gs}	--	0.18	--	
Gate Drain Charge		Q_{gd}	--	0.6	--	
Source-Drain Diode Ratings and Characteristics (Note 2)						
Forward Voltage	$V_{GS}=0V, I_F=1A$	V_{SD}	--	0.8	1.3	V
Continuous Source Current	Integral reverse diode in the MOSFET	I_S	--	--	2.5	A
Pulsed Current (Note 1)		I_{SM}	--	--	10	A





Notes:

1. Pulse test; pulse width ≤ 300 μs, duty cycle ≤ 2%.
2. Guaranteed by design, not subject to production testing.
3. Independent of operating temperature

TYPICAL CHARACTERISTICS




TYPICAL CHARACTERISTICS



Package Outline Dimensions (unit: mm)

DFN1006-3



Mounting Pad Layout (unit: mm)

