








REAR VIEW




TOP VIEW

PCB LAYOUT



SPECIFICATION

- 1.Rating DC 20V 15A.
- 2.Contact resistance: $\leq 30\text{m}\Omega$,
- 3.Insulation resistance: $\geq 100\text{M}\Omega$ (DC250V)
- 4.Withstand voltage: 500VAC ;
- 5.Insertion and extraction force. 3-20N;
- 6.life test: 5,000 cycles



Washer

⑥	Washer	1	SPCC	Ni-Plating
⑤	Nut	1	H59 BRASS	Ag-Plating
④	Tip spring	1	Bronze C5191 t=0.2	Ag-Plating
③	PIN	1	H59 BRASS	Ag-Plating
②	Housing	1	PBT	Black
①	Bushing	1	H59 BRASS	
NO.	DESCRIPTION	QTY	MATERIAL	PLATING

							ANGLE	±5°	Designed:	Checked:	Approved:	Date:	MODEL TYPE:
							30 ~	±0.30					DC JACK
							10 ~ 30	±0.20					PART NO.
							~ 10	±0.10					CAX-DC-230-2.5-L8.5-15A-XL
—	A/0		NEW										UNIT:
ECN NO	REV	DATE	DESCRIPTION	CHANGE	CHECK	APPRO.	UNSPECIFIED TOLERANCE						SCALE:
1													VIEW:
													Edition:
													mm
													1:1
													⊗
													A/1

浙江创都电子科技有限公司

UNIT:	SCALE:	VIEW:	Edition:
mm	1:1	⊗	A/1