


Features

- 10 μ A Current at no Load
- $\pm 1\%$ Output Accuracy
- 500mA Output Current
- Current Limit Protection

Applications

- Industrial Controls
- Home Automation
- Wireless power tools
- Motor driver and control board

PIN CONFIGURATION




SOT23-5

Pin Number	Pin Name	Pin Function
SOT23-5		
1	VIN	Input of Supply Voltage
2	GND	Ground
3	EN	Enable Control Input
4	BYPASS	BYPASS pin to achieve low noise performance, 1.2V
5	VOUT	Output of the Regulator

Ordering Information

TPCAT6219-280TDGT3



Absolute Maximum Ratings


over operating free-air temperature range (unless otherwise noted)

		MIN	MAX	UNIT
V _{IN}	Continuous input voltage range	0	6	V
V _{OUT}	Output voltage range	-0.3	V _{IN} +0.3	
EN	EN pin voltage range	-0.3	V _{IN} +0.3	
Current	Maximum output current	Internally limited		mA
Temperature	Operating junction, T _J	-40	150	°C
	Storage, T _{stg}	-50	150	


ESD Ratings

			VALUE	UNIT
V (ESD)	Electrostatic discharge	Human body model (HBM)	±3000	V
		Charged device model (CDM)	±500	

BLOCK DIAGRAM



Typical Application Circuit



Electrical Characteristics







(VIN=15V, VEN=5V, TA=25°C, unless otherwise specified)

PARAMETER	SYMBOL	TEST Conditions	MIN	TYP	MAX	UNIT
Supply Voltage	VIN		2.3	--	5.5	V
Output current	IOUT		0	--	500	mA
DC Output Voltage Accuracy		IOUT = 0.1mA	-2	--	2	%
Dropout Voltage (VIN-VOUT)	IOUT = 100mA	VOUT = 1.25V	--	108	--	mV
		VOUT = 1.80V	--	102	--	
		VOUT = 2.50V	--	98	--	
		VOUT = 2.80V	--	91	--	
		VOUT = 2.85V	--	90	--	
		VOUT = 3.00V	--	88	--	
		VOUT = 3.30V	--	85	--	
Ground Current (IOUT = 0mA)	IQ	VOUT = 3.3V	--	--	10	uA
Shutdown Ground Current	ISD	VEN = 0V,	--	0.01	0.5	
VOUT Shutdown Leakage Current	ILEAK	VOUT = 0V	--	0.01	0.5	
Enable Threshold Voltage	VIH	EN Rising	1.1	--	--	V
	VIL	EN Falling	--	--	0.4	
EN Input Current	IEN	VEN = 5.5V	--	10	100	nA
Line Regulation	ΔLINE	IOUT = 1mA, 2.3 ≤ VIN ≤ 5.5V	--	0.3	--	%
Load Regulation	ΔLOAD	10mA ≤ IOUT ≤ 100mA	--	0.3	--	
Output Current Limit	ILIM	VOUT = 0.9 × VOUT(NOM)	500	550	--	mA
Power Supply Rejection Ratio	PSRR	VOUT = 3.3V, IOUT = 30mA, VIN = 5.5V, f = 1kHz	--	68	--	dB
Thermal Shutdown Temperature	TSD	IOUT = 10mA	--	160	--	°C
Thermal Shutdown Hysteresis	ΔTSD		--	10	--	
Package Thermal Resistance (Note 1)	TJA	Thermal Resistance Junction-to-Ambient	--	200	--	°C/W

Note: 1. Test condition: For SOT23-5, the device is mounted on FR-4 substrate PC board, with minimum recommended pad layout.


Typical Operating Characteristics (shown for 2.80 V output option)

Unless otherwise specified: $T_A = 25^\circ\text{C}$, $V_{IN} = 3.85\text{ V}$, $C_{BYP} = 10\text{ nF}$, $C_{OUT} = 1\text{ }\mu\text{F}$, $C_{IN} = 1\text{ }\mu\text{F}$ all voltage options, EN pin tied to V_{IN} .



Package information

SOT23-5



参数	尺寸 (mm)		尺寸 (Inch)	
	最小值	最大值	最小值	最大值
A	0.9	1.45	0.0354	0.0570
A1	0	0.15	0	0.0059
A2	0.9	1.3	0.0354	0.0511
B	0.2	0.5	0.0078	0.0196
C	0.09	0.26	0.0035	0.0102
D	2.7	3.10	0.1062	0.1220
E	2.2	3.2	0.0866	0.1181
E1	1.30	1.80	0.0511	0.0708
e	0.95REF		0.0374REF	
e1	1.90REF		0.0748REF	
L	0.10	0.60	0.0039	0.0236
a°	0°	30°	0°	30°