

PRODUCT SPECIFICATION

SPEC. NO: C-2603-01

DATE: Mar.7,2026

CUSTOMER'S PRODUCT NAME:

EMTEK PRODUCT NAME:

BCMF201208900M00

THIS SPECIFICATION IS:

- ☐ FULLY ACCEPTED
- ☐ DENIED
- ☐ ACCEPTED UNDER THE FOLLOWING CONDITIONS



SIGNATURE: DATE:

NAME(PRINT):

TITLE:

本文件內容全部或部份,未經兆欣科技股份有限公司
同意不得以任何形式複製或其他用途
*All rights reserved. This document or parts
thereof, may not be reproduced by any
means or used in any manner without
written permission of EMTEK CO.,LTD.*



EMTEK CO., LTD.

FACTORY:

39,Chingao Rd.,(305)Hsinpu,
Hsinchu Hsien,Taiwan,R.O.C

TEL: 03-5894-433

FAX: 03-5894-523

PRODUCT SPECIFICATION

SPEC. NO.

C-2603-01

1. Features

- Effective for suppressing common mode noise and almost no effect for high speed differential data line.
- Ultra low profile (2.0x1.2x0.8mm).
- Ceramic multilayer type SMD component.
- Non-polarized product.
- It is a product conforming to RoHS directive.



2. Application

- LVDS lines in notebook computers.
- USB2.0, IEEE1394, DVI, HDMI lines in PDP, LCD TV, DVD Player, PC, Audio player, DSC.
- MDDI, MIPI in mobile phone.

3. Part numbering

B	-	CMF	-	201208	-	900	-	M	-	00
Grade		Product Series		Dimensions(mm)		Impedance (Ω)		Tolerance		Control code

4. Appearance and Dimensions



Unit : mm

PRODUCT SPECIFICATION

SPEC. NO.

C-2603-01

5. Rating


NOTE:

- Operating temperature: -40℃ ~ +85℃

ELECTRICAL CHARACTERISTICS

Part No.	Impedance (Ω)	Test Freq	DCR (Ω)	Rated Current (mA)	Rated Voltage (V) Dc	Insulation Resistance (MΩ)
BCMF201208900M00	90 (±25%)	100MHz	Max 4.0	Max 100	10	Min 10

Typical Eleectrical Characteristics





PRODUCT SPECIFICATION

SPEC. NO.

C-2603-01

6. Reliable Performance

No	ITEM	REQUIREMENT	TEST CONDITION
1	Reflow soldering	No mechanical damage. More than 50% of the terminal Electrode shall be covered with new solder.	-Pre-heating temperature : 160 ~ 185°C time : 110 ±10 sec -Soldering temperature : 220°C 이상 time : 40 ±10 sec -Peak temperature : max 260°C time : max 10sec.
2	Bending Strength test	No mechanical damage. impedance change: within ±30%	
3	Adhesive strength of Terminal electrode	Adhesion strength should be over 1kgf	
4	Thermal shock	No mechanical damage. impedance change: within ±30%	Step 1: -40 ±2°C 30 ±3min. Step 2: 85 ±2°C 30 ±3min. Number of cycle : 100 times Then measured after exposure in the room condition for 24±2hrs
5	Heat Load resistance	No mechanical damage. impedance change: within ±30%	Temperature : 85 ±2°C Applied Current : Rated Current Time: 168hrs Then measured after exposure in the room condition for 24±2hrs
6	Humidity load resistance	No mechanical damage. impedance change: within ±30%	Temperature : 85 ±2°C Humidity : 85%RH ± 5%RH Applied Current : Rated Current Time: 168hrs Then measured after exposure in the room condition for 24±2hrs
7	Low Temp. resistance	No mechanical damage. impedance change: within ±30%	Temperature : -40 ±2°C Time: 168hrs Then measured after exposure in the room condition for 24±2hrs



EMTEK CO., LTD.

PRODUCT SPECIFICATION

SPEC. NO.

C-2603-01

- Result

No	ITEM	REQUIREMENT	Sample Size	Ac, Re	Result
1	Reflow soldering	No mechanical damage. More than 50% of the terminal Electrode shall be covered with new solder.	10	0,1	OK
2	Bending Strength test.	No mechanical damage. impedance change: within $\pm 30\%$	10	0,1	OK
3	Adhesive strength of Terminal electrode	Adhesion strength should be over 1kgf	10	0,1	OK
4	Thermal shock	No mechanical damage. impedance change: within $\pm 30\%$	10	0,1	OK
5	Heat Load resistance	No mechanical damage. impedance change: within $\pm 30\%$	10	0,1	OK
6	Humidity Load resistance	No mechanical damage. impedance change: within $\pm 30\%$	10	0,1	OK
7	Low Temp. resistance	No mechanical damage. impedance change: within $\pm 30\%$	10	0,1	OK




PRODUCT SPECIFICATION

SPEC. NO.

C-2603-01

6.Recommended Soldering Conditions

6.1 RECOMMENDED SOLDERING PROFILE (Lead-free condition)



6.2 RECOMMENDED LEAD-FREE SOLDER PASTE

- Supplier : Tamura Donghwa
- Main composition : Sn-Ag-Cu
- Ratio of composition : 96.5%-3.0%-0.5%

6.3 RECOMMENDED HAND SOLDER

- Max Temperature: Max 380 °C(Max 5sec)



EMTEK CO., LTD.


PRODUCT SPECIFICATION

SPEC. NO.


C-2603-01

7. Packaging

7.1 TAPING FIGURE



7.2 CARRIER TAPE DIMENSIONS



Unit : mm

SYMBOL		A	B	W	F	E	P ₁	P ₂	P ₀	D	T
DIMENSION	21	1.55 ±0.05	2.3 ±0.05	8.0 ±0.1	3.5 ±0.05	1.75 ±0.05	4.0 ±0.1	2.0 ±0.05	4.0 ±0.1	1.55 ±0.03	0.95 ±0.05




EMTEK CO., LTD.

PRODUCT SPECIFICATION

SPEC. NO.

C-2603-01

7.3 REEL DIMENSIONS



(1) Reel Materials: Polystyrene

(2) Label

CODE	A	B	C	D	E	W	t	R
DIMENSION	$\phi 178 \pm 2$	Min. $\phi 50$	$\phi 13 \pm 0.5$	$\phi 20 \pm 0.8$	3.0 ± 0.5	10 ± 1.5	1.3 ± 0.2	1.0 ± 0.2

7.4 Packaging quantities

- Standard Packing Quantity per Reel ($\Phi 178$)

- Paper Tape: 4,000pcs

PRODUCT SPECIFICATION

SPEC. NO.

C-2603-01

8.Storage

(1) Storage period

Use the products within 24 months after delivered. Solderability should be checked if this period is exceeded.

(2) Storage conditions

●Storage temperature: 20~25℃

●Storage environment: 20~25℃ humidity: RH40%~60%

(3) Delivery

Care should be taken when transporting or handling product to avoid excessive vibration or mechanical shock.