



MK-11C02-G015-A A

Horizontal

G-Switch P/N



Switch Height (mm)

G015=1.5mm
G020=2.0mm

Operating Force


A=160±50gf
B=200±50gf

Switch lifetime (Force)
A=Base With Pilot
N=Non Pilot




P.C.B MOUNTING PATTERN DIMENSION

the following soldering are recommended for reflow soldering



CIRCUIT DIAGRAM



RoHS
Compliant
2002/95/EC



SCALE: 1:1 UNIT: mm
SIZE: A4

Unless otherwise
General Tolerance:
X. ±0.30
X.x ±0.20
X.xx ±0.15
X.xxx ±0.10
Angles ±3°

Title: Horizontal Mini Slide Switch 5.0×2.75×1.4mm

Molde Code: MK-11C02-G015-AA

DRAWN	CHECKED	APPROVED	DATE
Xia	Chen	Chen	2022.11.01

b-Switch 品赞科技®

REV: A0 SHEET: 1/1

G-Switch Specification:

1. Operating temperature range: -40℃ to +85℃
2. Rating: 0.3A, 5V DC
3. Insulation resistance: 100MΩ min. 100V DC
4. Dielectric strength: 250V AC for 1 min
5. Contact resistance: 100mΩ max.
6. Contact arrangement: 1P2T
7. Travel: 1.2±0.1mm
8. Switch lifetime: 10,000 cycles