

深圳市晶科鑫实业有限公司



样品承认书

客户代码:	
物料名称:	贴片钟振
规格型号:	SMD2520 OSC 6PIN 156.250MHZ 3.3V - 40~85℃ LVPECL
P N/ SJK:	2N156250G33PC
环保属性:	☒ RoHS ☒ REACH ☒ HF ☐ PAHS ☐ 其它
版 次:	A1 2025-5-10 初版
湿敏等级:	一级

承 认 签 章					
供 应 商 承 认			() 公 司 承 认		
制 定	审 核	核 准	工 程 师	审 核	批 准
贺丹斌	李相同	刘惠光			
SJK 支持			盖章签署		
F A E _ E M A I L			日 期		
日 期					
备注：					


ELECTRICAL SPECIFICATIONS

Parmeters	Condition\Model	2N
Fan Out Type		LVPECL
Supply Voltage		3.3V±10%
Frequency		156.250MHz
Operating Temperature		-40℃ to +85℃
Current		80mA Max
Frequency Stability	All Conditions	±30ppm
Output Voltage	Vol	Vcc-1.825min/Vcc-1.62V max
RL=50 ohms to (Vcc-2V)	VoH	Vcc-1.085min/Vcc-0.88V max
Rise/Fall Time	20%~80%	0.5ns Max
Duty Cycle(@Vcc-1.3V)		50±10%
Storge Temperature		-55~+125℃
Start-upTime		10ms Max
Aging		±3ppm (first year at 25℃)
Jitter(12kHz to 20MHz)		0.15ps
Input Voltage	VIH	Vcc*0.7V Min
	VIL	Vcc*0.3V Max

Crystal oscillator SMD LVPECL Output 2.5×2.0×0.95mm 2N Series




DIMENSION (Unit: mm)




MARK




MEASUREMENT CIRCUIT



WAVEFORM CONDITIONS




REFLOW CONDITION




The reflow temperature profile may vary depending on the product model, specifications and frequency range. Refer to the individual product specifications for details

CARRIER TYPE



REEL



RELIABILITY TEST SPECIFICATIONS

Test item	Equipment	Condition	Specification
1.SOLDERABILITY TEST	SJK-REL001、RC-328A	TP:260℃ TsMax: 200℃ TsMin: 150℃ 2 time 	MIL-STD-883E Method 2003.7
2. HERMETICITY TEST	HELIOT-306S	Pressurized 0.4~0.5Mpa ethanol sealed tank for 10 minutes	MIL-STD-883E Method 1014.10
3. VIBRATION TEST	HG-V4、S&A 250B	Enable Crystal(10g) from 10-55-10Hz,X、Y、Z horizontal,1 Minute vibration/time, 1time/ 2 hours.	MIL-STD-883E Method 2007.3
4. MECHANICAL SHOCK	HPC-200、S&A 250B	Enable Crystal 50G(490m/s ²) time=11 ms speed=3.4 m/s half sine wave oscillation	JIS C6701
5. DROP TEST	HARD BOARD.S&A250B	75cm High,3 times on hard board	MIL-STD-202F Method 213B
6. HIGH&LOW TEMP STORAGE TEST(Static test)	H-PTH-80CK & HM101-3ABN, S&A 350B/250B	High temperature: 125℃±2℃,1000hr; Low temperature:-40℃±3℃,1000hrs	MIL-STD883C, METHOD 1011.8
7. TEMP & HUM CYCLING TEST	H-PTH-80CK CHAMBE, S&A 350B/250B	Temperature:-10℃±2℃~65℃±2℃,Humidity:93±3%,1 cycle need 24 hrs. 5cycles.	MIL-STD-883E Method 1005.8
8. HIGH TEM. & HUM.STORAGE TEST	H-PTH-80CK CHAMBE, S&A350B/250B	Temperature:85℃±2℃, Humidity:85+3,-2%,Store 96 hrs	JIS C6701
9. AGING TEST	H-PTH-80CK CHAMBE, S&A350B/250	Temperature:85℃±2℃, Store 1000 hrs	JIS C5023